


Geberit Mapress Stainless Steel T-piece, reduced (silicone-free)



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water $\leq 120\text{ }^{\circ}\text{C}$
- For saturated steam $\leq 120\text{ }^{\circ}\text{C}$
- For service water and process water
- For treated water
- For grey and black water with a pH value ≥ 5.5

- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
81204	15 / 12 / 15	18	15	18	90	6.8	4.1	3.4	3.4	1.4	2.1	1.4
81206	20 / 12 / 20	22	15	22	90	7.4	4.3	3.7	3.7	1.6	2.3	1.6
81207	20 / 15 / 20	22	18	22	90	7.4	4.3	3.7	3.7	1.6	2.3	1.6
81209	25 / 12 / 25	28	15	28	90	8.4	4.6	4.2	4.2	1.9	2.6	1.9

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
81210	25 / 15 / 25	28	18	28	90	8.4	4.6	4.2	4.2	1.9	2.6	1.9
81211	25 / 20 / 25	28	22	28	90	8.4	4.7	4.2	4.2	1.9	2.6	1.9
81212	32 / 12 / 32	35	15	35	90	10	4.9	5	5	2.4	2.9	2.4
81213	32 / 15 / 32	35	18	35	90	10	4.9	5	5	2.4	2.9	2.4
81214	32 / 20 / 32	35	22	35	90	10	5	5	5	2.4	2.9	2.4
81215	32 / 25 / 32	35	28	35	90	10	5.3	5	5	2.4	3	2.4
81216	40 / 12 / 40	42	15	42	90	11.4	5.3	5.7	5.7	2.7	3.3	2.7
81217	40 / 15 / 40	42	18	42	90	11.4	5.3	5.7	5.7	2.7	3.3	2.7
81218	40 / 20 / 40	42	22	42	90	11.4	5.4	5.7	5.7	2.7	3.3	2.7
81219	40 / 25 / 40	42	28	42	90	11.4	5.7	5.7	5.7	2.7	3.4	2.7
81220	40 / 32 / 40	42	35	42	90	11.4	6.1	5.7	5.7	2.7	3.5	2.7
81221	50 / 12 / 50	54	15	54	90	13.8	5.9	6.9	6.9	3.4	3.9	3.4
81222	50 / 15 / 50	54	18	54	90	13.8	5.9	6.9	6.9	3.4	3.9	3.4

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
81223	50 / 20 / 50	54	22	54	90	13.8	6	6.9	6.9	3.4	3.9	3.4
81224	50 / 25 / 50	54	28	54	90	13.8	6.3	6.9	6.9	3.4	4	3.4
81225	50 / 32 / 50	54	35	54	90	13.8	6.7	6.9	6.9	3.4	4.1	3.4
81226	50 / 40 / 50	54	42	54	90	13.8	7.1	6.9	6.9	3.4	4.1	3.4
81229	65 / 20 / 65	76.1	22	76.1	90	23	7.2	11.5	11.5	6.2	5.1	6.2
81230	65 / 25 / 65	76.1	28	76.1	90	23	7.5	11.5	11.5	6.2	5.2	6.2
81231	65 / 32 / 65	76.1	35	76.1	90	23	7.9	11.5	11.5	6.2	5.3	6.2
81232	65 / 40 / 65	76.1	42	76.1	90	23	8.3	11.5	11.5	6.2	5.3	6.2
81233	65 / 50 / 65	76.1	54	76.1	90	23	8.9	11.5	11.5	6.2	5.4	6.2
81236	80 / 20 / 80	88.9	22	88.9	90	26	7.8	13	13	7	5.7	7
81237	80 / 25 / 80	88.9	28	88.9	90	26	8.1	13	13	7	5.8	7
81238	80 / 32 / 80	88.9	35	88.9	90	26	8.5	13	13	7	5.9	7
81239	80 / 40 / 80	88.9	42	88.9	90	26	8.9	13	13	7	5.9	7

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
81240	80 / 50 / 80	88.9	54	88.9	90	26	9.5	13	13	7	6	7
81241	80 / 65 / 80	88.9	76.1	88.9	90	26	11.6	13	13	7	6.3	7
81244	100 / 20 / 100	108	22	108	90	31	8.8	15.5	15.5	8	6.7	8
81245	100 / 25 / 100	108	28	108	90	31	9.1	15.5	15.5	8	6.8	8
81246	100 / 32 / 100	108	35	108	90	31	9.5	15.5	15.5	8	6.9	8
81247	100 / 40 / 100	108	42	108	90	31	9.9	15.5	15.5	8	6.9	8
81248	100 / 50 / 100	108	54	108	90	31	10.5	15.5	15.5	8	7	8
81249	100 / 65 / 100	108	76.1	108	90	31	12.6	15.5	15.5	8	7.3	8
81250	100 / 80 / 100	108	88.9	108	90	31	13.7	15.5	15.5	8	7.7	8