

# CHE 2-26 18.0-EC/5.0 Set

Cordless rotary hammer drill 18,0 V

Order no. 478474

GTIN 4030293213685



- + Brushless motor with greater efficiency and a longer service life
- + Powerful motor with 2.6 joules of impact energy and a high rate of removal
- + Function switch with four functions: drilling, hammer drilling, chiselling, chisel adjustment
- + Rotation stop for chiselling
- + Ideal for daily use for drilling and chiselling in concrete, brickwork, timber and metal
- + Drilling chuck can be removed without tools
- + Quick tool change: universal application, with SDS Plus drill chuck or 13 mm quick-release chuck
- + Electronic management system (EMS) protects the machine, extends the service life, and increases efficiency
- + Decoupled, ergonomic handle with rubberised grip surface. Vibrations are reduced by a sprung damper and additional vibration damping between the housing and handle
- + Accelerator switch with lock-on function
- + Robust gearbox housing made of die-cast aluminium
- + Electronic quick-acting brake
- + Non-rotating additional handle with depth stop
- + Integrated LED lamp with persistence function
- + LED battery capacity display
- + FLEX battery system: suitable for FLEX 18,0 V/5,0 Ah battery packs



## Technical data

Battery voltage	18.0 V
Battery capacity	5.0 / 8.0 Ah
Tool holder, drill and chisel	SDS-plus
Max. single impact energy	2.6 J
No-load speed	0 - 980 rpm
No-load blows	0 - 4350 1 rpm
Max. drilling diameter in concrete	26 mm
Max. drilling diameter in wood	30 mm
Max. drilling diameter in steel	13 mm
Number of supplied batteries	2 Cont.
With charger	Yes
Dimensions WxLxH	360 x 85 x 230 mm
Weight without battery pack	3.18 kg

## Standard equipment

- 1 Chuck (468835)
- 1 Handle (436364)
- 1 Depth stop (417769)
- 1 Rapid charger (417882)
- 1 Carrying case L-BOXX® (414093)
- 1 Case insert (488356)
- 2 Li-Ion rechargeable battery pack 18,0 V (532733)