

RN73C1E31K6BTD

✓ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 1-2176263-2

31.6K ohm, Surface Mount Precision Resistor, Thin Film, 0402, .063

W, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RN73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 31.6K  $\Omega$

Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0402

Power Rating: .063 W

Features

Product Type Features

|                   |                    |
|-------------------|--------------------|
| Resistor Type     | Precision Resistor |
| Element Type      | Thin Film          |
| Package Size Code | 0402               |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                           |
|-----------------------------|---------------------------|
| Operating Voltage           | 25 V                      |
| Resistance Value            | 31.6K $\Omega$            |
| Power Rating                | .063 W                    |
| Resistance Class            | 1k $\Omega$ – 1M $\Omega$ |
| Passive Component Tolerance | .1 %                      |

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Surface Mount Resistor Termination Type | Solder |
| Number of Terminations                  | 2      |



Dimensions

|                |                |
|----------------|----------------|
| Product Height | .3 mm[.012 in] |
| Product Length | 1 mm[.039 in]  |
| Product Width  | .5 mm[.02 in]  |

Usage Conditions

|                         |            |
|-------------------------|------------|
| Temperature Coefficient | ±10 ppm/°C |
|-------------------------|------------|

Industry Standards

|                            |   |
|----------------------------|---|
| Moisture Sensitivity Level | 1 |
|----------------------------|---|

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RN73C1E31K6BTD

31.6K ohm, Surface Mount Precision Resistor, Thin Film, 0402, .063 W, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RN73



TE Part # 1-2176263-3  
RN 0402 32K4 0.1% 10PPM 5K RL

TE Part # 1-2176263-1  
RN 0402 30K9 0.1% 10PPM 5K RL

Also in the Series | [Holsworthy RN73](#)

[Surface Mount Resistors\(3641\)](#)

Customers Also Bought

TE Part #E88361-000  
T1K-095095-10-9

TE Part #6-1879746-4  
RP 1J 26K7 0.1% 15PPM CUT LENGTH

TE Part #3-1614352-5  
RN 0603 26K7 0.1% 10PPM CUT LENGTH

TE Part #CAT-M5833-C1121  
MICRO-MATCH STD MOW TO MOW CABLE ASSY

TE Part #1-1879353-7  
RR02 5% 20K AMMO

TE Part #1-2176347-5  
CRGCQ 2010 150R 1%

TE Part #1586768-6  
6P VERT HDR VAL-U-LOK GW

TE Part #338728-4  
MICROM. MOB SMD CON

TE Part #1-796690-0  
TERMI-BLOK PCB MOUNT 10P





Documents

Product Drawings

[RN 0402 31K6 0.1% 10PPM 5K RL](#)

English

Datasheets & Catalog Pages

[High Precision Resistors \(SMD\) - Type RN73 Series - Tyco Electronics Passives](#)

English