



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Coverpart Kit**

Primary Product Color: **Black**

Primary Product Material: **Nylon**

Operating Temperature (Max): **85 °C [185 °F]**

Operating Temperature Range: **-20 – 85 °C [-4 – 185 °F]**

Features

Product Type Features

Sealable	No
Connector Cover Type	Strain Relief Coverpart Kit

Body Features

Primary Product Color	Black
Primary Product Material	Nylon

Housing Features

Compatible With Connector Shape	Rectangular
---------------------------------	-------------

Usage Conditions

Compatible With Connector Style	Receptacle
Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]

Packaging Features

Packaging Method	Box & Carton
Packaging Quantity	500



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #CAT-D625-L52
DIP Socket: Low Profile, Stamped & Formed, Open, Tin



TE Part #1969598-2
2P FH PLUG VAL-U-LOK V2



TE Part #3-640427-2
02P MTA156 CONN ASSY 20AWG YEL



TE Part #2238020-1
VAL-U-LOK PIN BR TN 22-18 LP




TE Part #2238021-1
VAL-U-LOK SKT BR SN 22-18 LP



TE Part #794616-4
FREE HANG DBL ROW HSG 4 POS



TE Part #1-794612-1
PIN CONT 20-24 15 GOLD L/P



TE Part #280630
AMPMODU II COSI PIN HSG, SGL ROW, 6 POS.



TE Part #3-640426-6
06P MTA156 CONN ASSY 18AWG ORA

Documents

Product Drawings

4 pos. coverpart (kit) for P/N 794616-4

English

CAD Files

Customer View Model

ENG_CVM_CVM_293735-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_293735-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_293735-1_A.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English