

Description

STAINLESS STEEL TOP PLATE CASTOR, POLYAMIDE 160MM

Fixed

KF5BA160-77L



Part Number

Swivel

KP5BA160-77L




Swivel and brake

KP5BD160-77L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	160 mm		
Overall Height H	197 mm ±1		
Size of plate A X B	129 x 106 mm±1		
Plate hole centres a x b	105 x 80 mm±0,3		
Plate hole	11 mm		
Offset F ±1	\	52 mm	52 mm
Width of Tread	45 mm±0,5		
Hardness of tread	shore A ± 83°		
Load capacity	300 Kg		
Weight	1,1 kg	1,5 kg	1,8 kg
Temperature	- 20 / + 80 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
 Fastening by top plate.
 Total lock. Metal pedal.

Wheel :

Wheel of White Polyamide 6. Non marking.
 Hub : Plain bore.

Features :

Low starting effort. High load capacity.
 Lightweight, highly resistant to knocks and other impacts as well as a great many chemical substances.
 Corrosion resistant, easy to clean. Specially designed for humid environments.
 Suited for Food industry, Hospital or Industrial Kitchen equipment.
 Non staining.
 Medium duty.