

TF-FS200

Torque wrench TORCOFIX FS

without pre-set

Code	ETIM
3288285	EC002132
EAN	UNSPSC
4010886965610	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



Article description

- Controlled screw tightening in the range of 40 - 200 Nm / 30 -150 lbf·ft
- Triggering and robust pipe torque wrench with fixed setting
- Versions with SE 14x18 insert socket
- For controlled right- and left-hand tightening (insert tool for change of direction)
- Proven and robust release mechanism
- Compact Design
- New ergonomic handle
- Tamper-proof Cap at the End of the Handle
- Factory depth gauge: 25 mm (14x18 mm)
- Operation only with end fittings with standardised depth gauges, otherwise inaccuracies can arise
- Depending on the application, access is possible from the front (e.g. open-end fitting) or side (e.g. reversible ratchet and socket).
- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/- 3 % deviation and thus with a greater precision than the standard-stipulated +/- 4 %
- Incl. traceable test certificate (DIN EN ISO 6789-2:2017)
- If fixed setting at the factory is desired is required, please state the Nm / lbf·ft value when ordering (price on request)
- OPTIONAL: 2in1 Adjustment and Locking Tool TF-EFS25 (Code: 3254941)

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [lbf·ft]	30 lbf·ft - 150 lbf·ft
Net weight [kg]	0,75 kg	Drive connector rectangular	14 x 18 mm
Total length [mm]	410 mm	Backup	Catch lock
Total width [mm]	33 mm	Trigger mechanism	Short path triggering
Total height [mm]	25 mm	Precision +/-	+/- 3 %
Depth gauge [metric]	25,0 mm	Direction of tightening	Left and right
Torque (min.) [N·m]	40 Nm	Fixed setting	yes
Torque (max.) [N·m]	200 Nm	Test certificate	DIN EN ISO 6789-2:2017
Torque (min.) [lbf·ft]	30 lbf·ft	Calibration length	345,5 mm
Torque (max.) [lbf·ft]	150 lbf·ft	Storage/Content	Plastic box
Torque range (min./max.) [Nm]	40 Nm - 200 Nm		