

CP0010 v3.14 RS 187-6955, 227-4427, 567-890**SAFETY DATA SHEET
RS Pro Isopropyl Alcohol Cleaner**

According to Regulation (EC) No 1907/2006, Annex II, as amended. Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product name RS Pro Isopropyl Alcohol Cleaner

Product number 227-4427, 567-890, 187-6955

UFI UFI: JA80-Y0KU-U00X-JVTF

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier RS Components Ltd
Birchington Road,
Corby,
Northants
NN17 9RS
+44 (0) 845 850 9900
RCustomerServicesUK@rs-components.com

RS Components Ltd
Glenview Industrial Estate
Herberton Road
Rialto
Dublin 12
+353 (0) 1 415 3100
enquiries.ie@rs-components.com

1.4. Emergency telephone number

Emergency telephone +44 (0)1865 407333
+44 1235 239670

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification (EC 1272/2008)**

Physical hazards Flam. Liq. 2 - H225

Health hazards Eye Irrit. 2 - H319 STOT SE 3 - H336

Environmental hazards Not Classified

2.2. Label elements**Hazard pictograms**

Signal word Danger

RS Pro Isopropyl Alcohol Cleaner

Hazard statements	H225 Highly flammable liquid and vapour. H319 Causes serious eye irritation. H336 May cause drowsiness or dizziness.
Precautionary statements	P102 Keep out of reach of children. P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P501 Dispose of contents/ container in accordance with national regulations.
Contains	Propan-2-ol
Supplementary precautionary statements	P240 Ground and bond container and receiving equipment. P241 Use explosion-proof electrical equipment. P242 Use non-sparking tools. P243 Take action to prevent static discharges. P261 Avoid breathing vapour/ spray. P264 Wash contaminated skin thoroughly after handling. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing. P312 Call a POISON CENTRE/doctor if you feel unwell. P337+P313 If eye irritation persists: Get medical advice/ attention. P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog to extinguish. P403+P233 Store in a well-ventilated place. Keep container tightly closed. P403+P235 Store in a well-ventilated place. Keep cool.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Propan-2-ol		60-100%
CAS number: 67-63-0	EC number: 200-661-7	REACH registration number: 01-2119457558-25-XXXX
Classification		
Flam. Liq. 2 - H225		
Eye Irrit. 2 - H319		
STOT SE 3 - H336		

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Get medical attention. Place unconscious person on their side in the recovery position and ensure breathing can take place.

RS Pro Isopropyl Alcohol Cleaner

Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Never give anything by mouth to an unconscious person. Place unconscious person on their side in the recovery position and ensure breathing can take place. Keep affected person under observation. Get medical attention if symptoms are severe or persist.
Skin contact	Rinse with water.
Eye contact	Rinse with water. Do not rub eye. Remove any contact lenses and open eyelids wide apart. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.
Ingestion	No specific symptoms known.
Skin contact	No specific symptoms known.
Eye contact	Irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up. Flammable liquid and vapour. Vapours may be ignited by a spark, a hot surface or an ember. Vapours may form explosive mixtures with air. Fire-water run-off in sewers may create fire or explosion hazard.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Keep upwind to avoid inhalation of gases, vapours, fumes and smoke. Ventilate closed spaces before entering them. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

RS Pro Isopropyl Alcohol Cleaner

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Do not touch or walk into spilled material. Evacuate area. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated. Avoid inhalation of vapours and spray/mists. Use suitable respiratory protection if ventilation is inadequate.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Do not allow material to enter confined spaces, due to the risk of explosion. Absorb small quantities with paper towels and evaporate in a safe place. Once evaporation is complete, place paper in a suitable waste disposal container and seal securely. Large Spillages: If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. The contaminated absorbent may pose the same hazard as the spilled material. Label the containers containing waste and contaminated materials and remove from the area as soon as possible. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store away from incompatible materials (see Section 10). Keep out of the reach of children. Keep away from food, drink and animal feeding stuffs. Keep away from oxidising materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.

Storage class Flammable liquid storage.

7.3. Specific end use(s)

RS Pro Isopropyl Alcohol Cleaner

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

Propan-2-ol

Long-term exposure limit (8-hour TWA): WEL 400 ppm 999 mg/m³

Short-term exposure limit (15-minute): WEL 500 ppm 1250 mg/m³

WEL = Workplace Exposure Limit

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation.

Eye/face protection

Avoid contact with eyes. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

No specific hand protection recommended.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Hygiene measures

Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.

Respiratory protection

No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.

Environmental exposure controls

Keep container tightly sealed when not in use. Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Colourless.
Odour	Characteristic.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	82°C
Flash point	12°C Closed cup.
Evaporation rate	1.5 (diethyl ether = 1)
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.

RS Pro Isopropyl Alcohol Cleaner

Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.7855 @ 20°C
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity See the other subsections of this section for further details.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions The following materials may react strongly with the product: Oxidising agents.

10.4. Conditions to avoid

Conditions to avoid Avoid heat, flames and other sources of ignition. Containers can burst violently or explode when heated, due to excessive pressure build-up. Static electricity and formation of sparks must be prevented.

10.5. Incompatible materials

Materials to avoid Oxidising materials. Acids - oxidising.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

RS Pro Isopropyl Alcohol Cleaner

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

None of the ingredients are listed or exempt.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development

Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H336 May cause drowsiness or dizziness.

Target organs Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.

Ingestion

No specific symptoms known.

Skin contact

No specific symptoms known.

Eye contact

Irritating to eyes.

Route of exposure

Ingestion Inhalation Skin and/or eye contact

Target organs

Central nervous system

SECTION 12: Ecological information

RS Pro Isopropyl Alcohol Cleaner

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

12.1. Toxicity

Toxicity Based on available data the classification criteria are not met.

12.2. Persistence and degradability

Persistence and degradability The degradability of the product is not known.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not available.

12.4. Mobility in soil

Mobility No data available.

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods Do not empty into drains. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

General For limited quantity packaging/limited load information, consult the relevant modal documentation using the data shown in this section.

14.1. UN number

UN No. (ADR/RID) 1219

UN No. (IMDG) 1219

UN No. (ICAO) 1219

UN No. (ADN) 1219

14.2. UN proper shipping name

Proper shipping name (ADR/RID) ISOPROPANOL (ISOPROPYL ALCOHOL)

Proper shipping name (IMDG) ISOPROPANOL (ISOPROPYL ALCOHOL)

Proper shipping name (ICAO) ISOPROPANOL (ISOPROPYL ALCOHOL)

Proper shipping name (ADN) ISOPROPANOL (ISOPROPYL ALCOHOL)

14.3. Transport hazard class(es)

RS Pro Isopropyl Alcohol Cleaner

ADR/RID class	3
ADR/RID classification code	F1
ADR/RID label	3
IMDG class	3
ICAO class/division	3
ADN class	3

Transport labels



14.4. Packing group

ADR/RID packing group	II
IMDG packing group	II
ICAO packing group	II
ADN packing group	II

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

EmS	F-E, S-D
ADR transport category	2
Emergency Action Code	•2YE
Hazard Identification Number (ADR/RID)	33
Tunnel restriction code	(D/E)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations	Health and Safety at Work etc. Act 1974 (as amended). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits.
----------------------	---

RS Pro Isopropyl Alcohol Cleaner

EU legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).
 Commission Regulation (EU) No 2015/830 of 28 May 2015.
 Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Abbreviations and acronyms used in the safety data sheet

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.
 ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways.
 RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail.
 IATA: International Air Transport Association.
 ICAO: Technical Instructions for the Safe Transport of Dangerous Goods by Air.
 IMDG: International Maritime Dangerous Goods.
 CAS: Chemical Abstracts Service.
 ATE: Acute Toxicity Estimate.
 LC₅₀: Lethal Concentration to 50 % of a test population.
 LD₅₀: Lethal Dose to 50% of a test population (Median Lethal Dose).
 EC₅₀: 50% of maximal Effective Concentration.
 PBT: Persistent, Bioaccumulative and Toxic substance.
 vPvB: Very Persistent and Very Bioaccumulative.

Classification abbreviations and acronyms

Flam. Liq. = Flammable liquid
 Eye Irrit. = Eye irritation
 STOT SE = Specific target organ toxicity-single exposure

Classification procedures according to Regulation (EC) 1272/2008

STOT SE 3 - H336: Eye Irrit. 2 - H319: : Calculation method. Flam. Liq. 2 - H225: : Expert judgement.

Training advice

Read and follow manufacturer's recommendations.

Issued by

Emily Kirk

Revision date

13/11/2019

Revision

1.3

SDS number

361

Hazard statements in full

H225 Highly flammable liquid and vapour.
 H319 Causes serious eye irritation.
 H336 May cause drowsiness or dizziness.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.