



## 24-litre pneumatic oil pump

**RQN8010**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:31



**DESCRIPTION****24-litre pneumatic oil pump**

Equipped with oil level gauge, 1.5 metre delivery hose, valve, filler tube and 2 solid rubber wheels.

Suitable for engine oil with a viscosity of SAE 24.

**SPECIFIC DATA**

|                 |                             |
|-----------------|-----------------------------|
| Designation     | 24-LITER PNEUMATIC OIL PUMP |
| Sales reference | RQN8010                     |
| Weight (kg)     | 15                          |
| Width (mm)      | 370                         |

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:31



|             |   |
|-------------|---|
| Length (mm) | 320                                       |
| Height (mm) | 780                                       |
| Guarantee   | M1   SAM Equipment and Machine Guarantee: |

**Guarantee applied****M1 | SAM Equipment and Machine Guarantee:**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:31

