

M18 FBTS75-552X

M18 FUEL™ 75 MM BELT SANDER

Compact design, with a flat front and side edge allows flush sanding capability

Captures 90% of dust either through the universal dust port or with the multi layered dust bag

Variable speed adjustable with a belt speed range from 230 to 410 m/s

Tool-free adjustable pommel allows for adjustment of the front handle letting the user find the optimum sanding position

Standard belt size of 75 x 457 mm

Tool-free belt change with easy adjustment of the belt roller allowing for precise belt alignment

LED lights are placed at the front and side to give 180° of illumination

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Belt speed [m/min]	230 - 410
Belt length (mm)	457
Belt width (mm)	75
Weight with battery pack (EPTA) (kg)	4.6 (M18 HB5.5)
Kit included	2 x M18 HB5.5 Battery packs, M12-18 FC Charger, HD Box
Article number	4933479615