


Technical data


22232EMW33C3
Spherical roller bearings



ULTAGE®

VISUAL (S)





PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	160 mm
D - External diameter	290 mm
B - Bearing/Inner ring width	80 mm
D1 - Inner diameter outer ring	258,7 mm
rs - Min fillet radius	3 mm
Number of lubrication holes	3
b - Groove width	16,94 mm
k - Hole diameter	8 mm
Radial clearance class	C3
Mass	23,2 kg

PRODUCT PERFORMANCE

C - Dynamic load	1220000000 mN
------------------	---------------



PRODUCT PERFORMANCE

C0 - Static load	1390000000 mN
Cu - Fatigue limit load	132000000 mN
e - Coefficient	0.25
Y0 - Static axial load coefficient	2.63
Y1 - Lower axial load coefficient	2.69
Y2 - Upper axial load coefficient	4
N ref - Reference thermal speed	12000 °/s
N lim - Mechanical Limit Speed	16800 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	473,15 °K

ABUTMENT

da min - Min shoulder diameter IR	174 mm
Da max - Max shoulder diameter OR	276 mm
ra max - Max shaft & housing fillet radius	2,5 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	Y1	0.67	Y2

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
1	Y0

The values for e, Y1, Y2 and Y0 are shown in the above table .

