

Product data sheet

Specifications



Repacked Workstation, New Unica,
flush, 2 x 8 modules horizontal,
antibacterial, white

NU171820W



This repacked option saves 3.679 over the
standard condition

Main

Range	New Unica
Product or component type	Workstation
Number of modules	2 x 8 modules
Mounting position	Horizontal
fixing mode	Embedment Claws

Complementary

Provided equipment	Cover frame Fixing frame
Device mounting	Flush
Cable entry	6 knock-outs 20 mm for diameter 6 knock-outs 25 mm for diameter 2 bottom cable entries 45 x 25 mm for size 20 mm for diameter 4 bottom cable entries 50 x 35 mm for size 25 mm for diameter
Fire resistance	850 °C, extinction time <30 s
Material	ABS (acrylonitrile butadiene-styrene): separator PC: box ABS (acrylonitrile butadiene-styrene): cover frame PC: tower
surface treatment	Antibacterial
Depth	62 mm
Width	230 mm
Height	165 mm
Product weight	0.468 kg
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
-------------------------	------

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.500 cm
Package 1 Width	25.500 cm
Package 1 Length	31.000 cm
Package 1 Weight	664.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	2
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.804 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

4 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

Ce89f989-36a8-4890-9b3e-79150ca1abc2

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No