


Geberit Mapress Carbon Steel T-piece with female thread



Example image



APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For extinguishing water (wet)
- For sprinklers (wet)
- For compressed air (oil purity class 3)

- For technical building systems, industry and shipbuilding

- Pressing socket with transparent protection plug

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Outside zinc-plated
- Seal ring made of CIIR, black

TECHNICAL DATA

Product material	Non-alloy steel 1.0034 E195 (EN 10305)
------------------	--

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
21301	10	12	3/8	12	90	5.6	3.3	2.8	2.8	1.1	2.3	1.1
21302	10 / 15 / 10	12	1/2	12	90	5.6	3.6	2.8	2.8	1.1	2.3	1.1
21304	12 / 15 / 12	15	1/2	15	90	6.4	3.7	3.2	3.2	1.2	2.4	1.2
21305	15	18	1/2	18	90	6.8	3.9	3.4	3.4	1.4	2.6	1.4
21307	20 / 15 / 20	22	1/2	22	90	7.4	4	3.7	3.7	1.6	2.7	1.6

Art. no.	DN	d, ø mm	R _p "	d1, ø mm	arc °	L cm	L1 cm	l cm	l2 cm	z cm	z1 cm	z2 cm
21308	20 / 20 / 20	22	3/4	22	90	7.4	4.4	3.7	3.7	1.6	2.8	1.6
21309	25 / 15 / 25	28	1/2	28	90	8.4	4.4	4.2	4.2	1.9	3.1	1.9
21310	25 / 20 / 25	28	3/4	28	90	8.4	4.7	4.2	4.2	1.9	3.2	1.9
21311	25	28	1	28	90	8.4	5.3	4.2	4.2	1.9	3.6	1.9
21312	32 / 15 / 32	35	1/2	35	90	10	4.8	5	5	2.4	3.5	2.4
21313	32 / 20 / 32	35	3/4	35	90	10	5.1	5	5	2.4	3.6	2.4
21314	32 / 25 / 32	35	1	35	90	10	5.6	5	5	2.4	3.9	2.4
21316	40 / 15 / 40	42	1/2	42	90	11.4	5.1	5.7	5.7	2.7	3.8	2.7
21317	40 / 20 / 40	42	3/4	42	90	11.4	5.4	5.7	5.7	2.7	3.9	2.7
21318	40 / 25 / 40	42	1	42	90	11.4	6	5.7	5.7	2.7	4.3	2.7
21320	50 / 15 / 50	54	1/2	54	90	13.8	5.7	6.9	6.9	3.4	4.4	3.4
21321	50 / 20 / 50	54	3/4	54	90	13.8	6	6.9	6.9	3.4	4.5	3.4
21322	50 / 25 / 50	54	1	54	90	13.8	6.6	6.9	6.9	3.4	4.9	3.4

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
21324	50	54	2	54	90	13.8	7.9	6.9	6.9	3.4	5.6	3.4
21325	65 / 20 / 65	66.7	3/4	66.7	90	22	6.4	11	11	6	4.9	6
21326	65 / 20 / 65	76.1	3/4	76.1	90	23	7.4	11.5	11.5	6.2	5.9	6.2
21329	65 / 50 / 65	76.1	2	76.1	90	23	9.1	11.5	11.5	6.2	6.8	6.2
21331	80 / 20 / 80	88.9	3/4	88.9	90	26	8	13	13	7	6.5	7
21334	80 / 50 / 80	88.9	2	88.9	90	26	9.7	13	13	7	7.4	7
21336	100 / 20 / 100	108	3/4	108	90	31	9	15.5	15.5	8	7.5	8