

# LS-WMTB-AL (29X8) BK - Cable marker



0831508

<https://www.phoenixcontact.com/gb/products/0831508>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Aluminum label, black, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: Assembly with cable ties, cable diameter: > 2.9 mm, Number of individual labels: 36, text field height: 8 mm, text field width: 29 mm



## Your advantages

- Aluminum cable marking for assembly with cable ties
- Suitable for large-surface marking of wires and cables, > 2.9 mm in diameter
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

## Commercial data

Item number	0831508
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG231D
Product key	BG231D
Catalog page	Page 189 (C-3-2019)
GTIN	4046356925105
Weight per piece (including packing)	73.97 g
Weight per piece (excluding packing)	65.8 g
Customs tariff number	76169990
Country of origin	CN

## Technical data

### Product properties

Product type	Conductor marking
Type	Rectangle
Type	Laser sheet

### Marking

Number of individual labels	36
Identification technology	Direct laser marking

### Dimensions

Width	8.5 mm
Length	47 mm
Material strength	0.80 mm

### External dimensions

Outside diameter	2.9 mm ... 136 mm
------------------	-------------------

### Text field

Text field width	29 mm
Text field height	8 mm

### Material specifications

RoHS compliant	yes
Color	black (RAL 9005)
Material	Aluminum
Components	free from silicone, halogen, and cadmium

### Cable/line

External cable diameter	> 2.90 mm
-------------------------	-----------

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed

# LS-WMTB-AL (29X8) BK - Cable marker



0831508

<https://www.phoenixcontact.com/gb/products/0831508>

n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

## Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

# LS-WMTB-AL (29X8) BK - Cable marker



0831508

<https://www.phoenixcontact.com/gb/products/0831508>

## Classifications

### ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

### ETIM

ETIM 9.0	EC001530
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# LS-WMTB-AL (29X8) BK - Cable marker



0831508

<https://www.phoenixcontact.com/gb/products/0831508>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)