




PIDG

TE Internal #: 52936-2
Spring Spade Terminal, 16 – 14 AWG, #8 / M4 Stud, 4.17 mm [.164 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially Insulated, PIDG

[View on TE.com >](#)

Terminals & Splices > Spade Terminals > PIDG Long Spring Spade Tongue Terminals



Spade Terminal Type: **Spring Spade Terminal**
Wire Size: **2050 – 5180 CMA**
Stud Size: **#8, M4**

[All PIDG Long Spring Spade Tongue Terminals \(50\)](#)

Features

Product Type Features

Stud Size	#8, M4
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Insulation Sleeve Color	Blue
Stripe Color	Blue

Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment



Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	4.17 mm[.164 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	21.84 mm[.86 in]
Compatible Insulation Diameter (Max)	4.62 mm[.182 in]
Compatible Insulation Diameter Range	2.92 – 4.62 mm[.115 – .182 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 2392022-1 BLUE BATTERY DAHT KIT 110V (47387-7)	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 169404 CERTI-LOK DIE	TE Part # 2063030-1 SDE DIESET, RBY, UL
TE Part # 47387-7 DAHT PG PIDG 16-12 ASSY	TE Part # 2392022-2 BLUE BATTERY DAHT KIT 220V (47387-7)	TE Part # 169400 CERTI-LOK FRAME W/O DIES	TE Part # 47387 DAHT PG PIDG 20-14 ASSY
TE Part # 59250 T-HEAD PIDG 26-14 ASSY	TE Part # 47807-1 DIES PIDG 16-14 DIE SET	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 58433-3 PRO CR ASSY, RBY IS9252
TE Part # 525691 DAHT PG PIDG 16-14 ASSY	TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY		



Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)




Hand Crimping Tools(2)



Knife Disconnects(11)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(41)

Customers Also Bought



TE Part #350922-6
PIN, MATE-N-LOK, UMNL



TE Part #36925
TERMINAL,SOLIS R 2/0 1/2



TE Part #36915
TERMINAL,SOLIS R 1/0 1/4



TE Part #647466-2
SL156 RECPT,AUNI/PHBZ,16AWG



TE Part #321879
TERMINAL,SOLIS R 4/0 7/16



TE Part #350699-7
UMNL SPLIT PIN AUNI/BR



TE Part #2-320630-2
TERMINAL,PIDG R 16-14HD 10



TE Part #350537-7
UMNL SOK 20-14 .0126 AUNI/BR



TE Part #350687-7
UMNL SPLIT PIN AUNI/BR



TE Part #320743
TERMINAL,SOLIS R 4 7/16



Documents

Product Drawings

TERMINAL,PIDG SPR SPD 16-14 8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_52936-2_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_52936-2_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_52936-2_V.3d_stp.zip

English

Customer View Model

ENG_CVM_52936-2_K.3d_igs.zip

English

Customer View Model

ENG_CVM_52936-2_K.3d_stp.zip

English

Customer View Model

ENG_CVM_52936-2_K.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

AMP* PIDG* (VINYL) & PLASTI-GRIP* SHORT SPRING SPADE TERMINALS FOR BAR

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English