

DIGITAL COLOR VARIFOCAL IR LED CAMERA 7769361

► CAUTION

- Do not open or strike this equipment. Sensitive electronics inside are vulnerable to excessive shock.
- Do not install the equipment near any naked flames or heat sources. Excessive heat could damage this unit.
- Do not cover cloth or to install this unit in poorly ventilated places. This may lead to overheating.
- Do not continue to operate if there appears to be fault.
If the unit ceases to function, contact qualified service personnel for help.
- Do not touch the power connection with wet hands. Risk of short circuit or electric shock.
- Do not damage the power cord or leave it under pressure. Risk of fire or shock circuit.



FEATURE

1/3" SONY 960H EXVIEW II SUPER HAD CCD HIGH RESOLUTION (70Φ, 36LEDs)

700TV Line (NTSC/PAL)

Auto White Balance

Automatic Gain Control


Dimension(mm) : 70Φ, 34LEDs

Power Source : DC 12V (6.5V - 28V)

Standard 1200mm, BNC/DC Jack

Minimum Illumination : 0.005Lux (F:1.2)

DC IRIS Vari-Focal Lens Type



SPECIFICATION	SCI136EHVF2812(NTSC)	SCI136EHVF2812(PAL)
Image Device	1/3" SONY 960H EXVIEW II SUPER HAD CCD	
Picture Elements	1020(H)×508(V)	1020(H)×596(V)
Scanning System	2:1 Interlace	
Sync System	Internal Synchronization	
Horizontal Resolution	700 TV Line	
Video Output	1Vp-p 75Ω	
S/N Ratio	52dB (AGC Off)	
Electronic Shutter	Auto	
BLC	Off	
Gamma Characteristic	Internal Synchronization: selectable (0.05~1.00)	
AGC	On	
Flickerless	Off	
LENS	2.8 - 12mm Varifocal Lens, DC IRIS	
Minimum Illumination	0.1Lux(Day), 0.005Lux(Night) (F:1.2)	
Power Consumption	DC12(6.5V~28V)/ 300mA(IR on)	
Operation Temperature	-10℃~ +50℃, RH95% Max (14°F~122°F)	
Storage Temperature	-20℃~ +60℃, RH95% Max	
Weight	Approx 695 g	
Housing	ALUMINUM	
Dimension(mm)	70Φ, 34LEDs	
Cable(option)	Standard 1200mm BNC/DC Jack	