



Main

Range of product	Ovalis C Series
Product or component type	TV/SAT/R socket
Device presentation	Mechanism with fixing frame
TV socket type	Individual
Type of packing	Paint cover
Sale per indivisible quantity	1
Condition of use	Indoor

Complementary

Device mounting	Flush
TV connector	Male IEC 9.52 mm
Radio connector	Female IEC 9.52 mm
SAT connector	F type
Number of inputs	1
Maximum branch attenuation	3 DB SAT signal 950...2400 MHz 3 DB TV signal 125...862 MHz 2.5 dB R signal 5...108 MHz
Minimum return loss	10 DB IN-OUT 10 DB TV 12 DB R 10 dB SAT
DC current flow	In SAT socket
Fixing mode	By screws By claws
Colour tint	Anthracite (RAL 7021)
Surface finish	Matt
Surface treatment	Painted
Rated current	350 mA
[Ue] rated operational voltage	24 V
Network type	DC
Connections - terminals	Screw terminals
Shape of screw head	Pozidriv No 1
Wire stripping length	8 mm
Type of cable	Coaxial
Cable outer diameter	7 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame Zinc alloy: casing
Height	71 mm
Width	71 mm
Depth	40 mm
Embedding depth	24 mm







The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Net weight	0.0634 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50083-4
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Bleach Liquid soap Window-cleaning fluid Alcohol Acetone Oil UV resistant Petrol

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Minimum percentage of recycled plastic content	0