


Handgewindebohrer

Hand Taps



Art. 105

DIN 351, HSSG, UNF, profilgeschliffen und hinterschliffen, für UNF-Gewinde (Unified-Feingewinde), Toleranz 2B.

DIN 351, HSSG, UNF, profile-ground and backed off, for UNF thread (Unified-fine thread), tolerance 2B.

Paar zu 2 Stück:
Vor- und Fertigschneider.

Pair of 2:
Taper and Plug.

CODE		UNF	mm	mm	mm	mm	mm	mm	mm	mm	g	EAN-CODE
												4026558.....
01501	No.1	No.0	80	1,52	32	7	2,5	2,1	1,25	1		015019
01502	No.2											015026
01503	Paar									2		015033
01504	No.1	No.1	72	1,85	32	7	2,5	2,1	1,55	1		015040
01505	No.2											015057
01506	Paar									2		015064
01507	No.1	No.2	64	2,18	36	8	2,8	2,1	1,85	1		015071
01508	No.2											015088
01509	Paar									2		015194
01510	No.1	No.3	56	2,52	40	8	2,8	2,1	2,10	1		015101
01511	No.2											015118
01512	Paar									2		015125
01513	No.1	No.4	48	2,85	40	10	3,5	2,7	2,40	1		015132
01514	No.2											015149
01515	Paar									2		015156
01516	No.1	No.5	44	3,18	40	12	3,5	2,7	2,70	1		015163
01517	No.2											015170
01518	Paar									2		015187
01519	No.1	No.6	40	3,51	45	14	4	3,0	3,0	2		015293
01520	No.2											015200
01521	Paar									4		015217
01522	No.1	No.8	36	4,17	45	14	4,5	3,4	3,5	2		015224
01523	No.2											015231
01524	Paar									4		015248
01525	No.1	No.10	32	4,83	48	16	6,0	4,9	4,1	4		015255
01526	No.2											015262
01527	Paar									8		015279
01528	No.1	No.12	28	5,49	50	16	6	4,9	4,65	7		015286
01529	No.2											015392
01530	Paar									14		015309
01531	No.1	1/4	28	6,35	50	16	6	4,9	5,5	11		015316
01532	No.2											015323
01533	Paar									22		015330
01534	No.1	5/16	24	7,94	56	16	6	4,9	6,9	14		015347
01535	No.2											015354
01536	Paar									28		015361
01537	No.1	3/8	24	9,53	56	16	7	5,5	8,5	21		015378
01538	No.2											015385
01539	Paar									42		015491
01540	No.1	7/16	20	11,11	63	18	8	6,2	9,9	30		015408
01541	No.2											015415
01542	Paar									60		015422
01543	No.1	1/2	20	12,70	70	20	9	7	11,5	41		015439
01544	No.2											015446
01545	Paar									82		015453
01546	No.1	9/16	18	14,29	70	22	11	9	13	54		015460
01547	No.2											015477
01548	Paar									108		015484
01549	No.1	5/8	18	15,88	70	22	12	9	14,6	84		015590
01550	No.2											015507
01551	Paar									168		015514
01552	No.1	3/4	16	19,05	80	22	14	11	17,5	120		015521
01553	No.2											015538
01554	Paar									240		015545
01555	No.1	7/8	14	22,23	90	28	18	14,5	20,5	180		015552
01556	No.2											015569
01557	Paar									360		015576