




Every part matters

EN



RS Pro DPDT 5V Polarised PCB Mount Relay

Stock Number: 193-5853



The RS Pro DPDT 5V polarised PCB mount relay is a drop in alternative solution to the obsolete Panasonic DF2, Omron G5A-234P, Fujitsu FBR46ND and all other BT53 type relays.





Contact Data		Characteristics	
Contact arrangement	2 pole C/O	Operate time	3ms max.
Contact resistance	100mΩ max at 10mA / 30mVdc	Release time	3ms max.
Contact material	AgNi + Au plated	Ambient temperature	-40°C to 85°C
Contact rating (Res. Load)	1A 30Vdc 0.5A 125Vac	Humidity	5% to 85% RH
Max. switching current	2A	Unit weight	1.24g
Max. Switching voltage	250Vac / 220Vdc	Coil Data (5V)	
Max. Switching power	62.5VA / 60W	Pick-up voltage Vdc max.	3.75V
Min. Applicable load	10mV 10μA	Drop-out voltage Vdc min.	0.5V
Mechanical endurance	1 x 10 ⁸ ops	Coil resistance Ω	178Ω
Electrical endurance	1 x 10 ⁵ ops (AgNi + Au plated, 0.5A 125Vac, resistive load, at 40°C, 1s on 9s off)	Nominal power mW	140mW
		Max voltage Vdc	7.5V