

# Endress+Hauser Capacitance level switch FTW32-A1D5CA0A

Simple and safe point level switch for a wide range of applications in liquids. The rope probe offers multipoint detection for up to 5 switch points.



Picture for reference only. Product appearance may vary based on configuration

The Liquipoint FTW32 is a point level detector for conductive liquids (from 10  $\mu\text{S}/\text{cm}$ ). With up to 5 rods, measuring tasks such as overflow protection, dry running protection, two-point control of pumps or multiple point detection can be implemented. The device does not require calibration and the absence of moving parts in the tank promotes a long service life and reliable operation.

- Detect up to five point levels with one probe
- Two-point control and additional MAX and MIN detection

### Configuration of FTW32-A1D5CA0A:

|                      |    |                           |
|----------------------|----|---------------------------|
| Approval:            | A  | Non-hazardous area        |
| Process Connection:  | 1  | Thread ISO228 G1-1/2, PPS |
| Sensing Point:       | D5 | 5x rope, 316Ti            |
| Probe Length:        | C  | 5000mm L                  |
| Cable Entry:         | A  | Gland M20                 |
| Electronics; Output: | 0  | Separate instrumentation  |
| Additional Option:   | A  | Basic version             |

Alternative part number: FTW32-A1D5CA0A