

IVR-L 65/12-1 TC

The IVR-L 65/12-1 Tc industrial vacuum cleaner is a compact entry-level machine with tilting chassis for vacuuming liquids and/or swarf in the metal processing industry.



Order no. 9.990-901.0

- Tilting chassis
- Compact design that takes up very little floor space
- Visual filling level indicator

Technical data

EAN code		4066529163905
Power supply	Ph / V / Hz	1 / 220 - 240 / 50 - 60
Air flow	l/s / m³/h	72 / 260
Vacuum	mbar / kPa	235 / 23.5
Container capacity	l	65
Container material		Steel
Rated input power	kW	1.2
Vacuuming type		Electric
Connection nominal diameter		DN 50
Accessory nominal diameter		DN 40 / DN
Main filter dust class		L
Filter area for main filter	m²	0.25
Weight without accessories	kg	40
Weight (with accessories)	kg	43.5
Weight incl. packaging	kg	43.5
Dimensions (L × W × H)	mm	737 × 532 × 1100



Ergonomic tilting chassis

- Sophisticated system for safe, manual, effortless emptying.
- Chassis system enables ergonomic tilted emptying using the roll-off mechanism.
- Quick and easy emptying of the container: just tip backwards and you are done!



High robustness, flexibility and modularity

- Machine and chassis very robust and equipped with high wall thicknesses.
- Rotatable hose connection with up to 360° rotatable pipe bend.
- Optionally available with overfill protection, strainer or accessories holder.



Reliable overfill protection

- A float effectively prevents overfilling of the collection container.
- Transparent hose for checking the amount of fluid absorbed.
- The hose is also used for easy emptying.

ACCESSORIES FOR IVR-L 65/12-1 TC

9.990-901.0



		Order no.	Description	
ACCESSORY SETS				
Accessory kit for liquids				
Liquid/solid accessory kit Expert DN40	1	9.990-878.0	Accessory kit DN40 for liquid vacuums: PU hose 3 m (9.989-617.0), handle (9.977-679.0), standard nozzle (9.988-401.0), reducer (9.981-231.0), surface nozzle 120 mm (9.988-118.0).	<input type="checkbox"/>
Accessory kit for liquids/chips				
Oil/swarf accessory kit DN40 Expert	2	9.990-880.0	Accessory kit DN40 for liquid vacuum and swarf vacuum: 3 m ME-PU hose (9.989-621.0), handle (9.977-679.0), standard nozzle (9.989-674.0), reducer (9.981-231.0), surface nozzle (9.988-118.0).	<input type="checkbox"/>
Advanced liquid floor cleaning set DN40	3	9.990-895.0	Advanced liquid floor cleaning set: EVA hose (9.990-925.0), handle (9.990-927.0), 2 × suction tube (9.990-931.0), floor nozzle (9.990-937.0), standard nozzle (9.980-773.0).	<input type="checkbox"/>
NOZZLES				
Standard nozzles				
Standard nozzle silicone DN40	4	9.988-401.0	Stretchy standard nozzle made from silicone, inner cone DN 40.	<input type="checkbox"/>
Floor nozzles				
Aluminium floor nozzle, el, 370 mm, DN40	5	9.989-682.0	Floor nozzle, 370 mm, made from aluminium. Electroconductive. DN 40.	<input type="checkbox"/>
Surface nozzles				
Silicone surface nozzle 120 mm DN40	6	9.988-118.0	Electroconductive rubber nozzle, angled, DN 40, suitable for use with foods.	<input type="checkbox"/>
Liquid nozzles				
Liquid nozzle 900 mm DN50	7	9.981-427.0	Bypass nozzle, DN 50, overall length: 1000 mm.	<input type="checkbox"/>
HOSES				
PU hoses				
Hose PU DN40 3 m	8	9.989-617.0	Oil-resistant, electroconductive PU hose, DN 40. Suitable for abrasive suction media and temperature-resistant up to 80 °C. Length: 3 m.	<input type="checkbox"/>
Hose PU DN50 3 m	9	9.989-619.0	Oil-resistant, electroconductive PU hose, DN 50. Suitable for abrasive suction media and temperature-resistant up to 80 °C. Length: 3 m.	<input type="checkbox"/>
HANDLES				
Handle DN 40	10	9.977-679.0	45° curved and electroconductive handle made from stainless steel. Inner cone DN 40.	<input type="checkbox"/>
Handle DN50, curved	11	9.977-678.0	Electroconductive and 45° curved handle made from stainless steel. Inner cone DN 50.	<input type="checkbox"/>
SUCTION TUBES				
Suction tube 850 mm DN 40	12	9.977-525.0	Steel extension tube, electroconductive, DN 40. Length: 850 mm.	<input type="checkbox"/>
ADAPTERS / REDUCERS / DISTRIBUTORS				
Reducers/expanders				
Reduction DN50 to DN40	13	9.981-231.0	Reducer from DN 50 to DN 40. Material: Steel. Electroconductive.	<input type="checkbox"/>
EMPTYING SUPPORTS				
Strainer baskets				
Filter basket, stainless steel, Ø 400 mm, 20 l	14	9.980-852.0	Filter basket, stainless steel, 20 l, hole diameter 1.5 mm. For the efficient separation of liquids and shavings.	<input type="checkbox"/>

■ Included in the scope of supply. □ Available accessories.

ACCESSORIES FOR IVR-L 65/12-1 TC

9.990-901.0



15

		Order no.	Description	
EMPTYING SUPPORTS				
Other emptying aids				
Overfill protection dia. 435 mm	15	9.982-118.0	Float insert, stainless steel, for overfill prevention with ball float, central suction.	<input type="checkbox"/>

Included in the scope of supply.
 Available accessories.