Parker Product Datasheet



Parker Parkrimp Medium Pressure Fittings - 46 Series - are permanent, crimp style hydraulic fittings that allow a quick assembly with our family of Parkrimp crimpers.

PART NUMBER: 19246-6-6
SHAPE: Straight
CONNECTION 2 TYPE: Female BSP Parallel Pipe - Swivel (60° Cone)
CONNECTION 2 SIZE: 3/8'
PORT TYPE: BSP
CONNECTION 1 SIZE: -6 Size

PRODUCT OVERVIEW

Parker's Parkrimp No-Skive medium pressure fittings - 46 series - are permanent, crimp style hydraulic fittings that allow a quick assembly with our family of Parkrimp crimpers. Assembly of No-Skive hose and fittings does not require removal of the outer cover of the hose. This eliminates premature hydraulic hose failure caused by skiving too long or short. 46 series fittings have chromium-6-free plating and are used with Parker wire braided hydraulic hoses such as Elite No-Skive with standard, tough or super tough cover, No-Skive Compact water cleaning hoses, No-Skive Compact Rail Hoses with fire retardant cover, No-Skive Compact Twin Constant Pressure hoses with tight bend radius and a lot more.
Parker Hannifin also meets the requirements of SAE J1273 and ISO 17165-2, which pay particular attention to matching the hose with the fittings and to their compatibility proven by the manufacturer.

Markets:
· Construction Equipment

· Injection Moulding
· Transportation
· Forestry and Agriculture
· Materials Handling
· Pulp and Paper

Features/Benefits:
· Matched hose und fitting system guarantees an approved and safe combination and the highest quality and safety
combined with the longest service life of the final product to the end-users.
· No-Skive technology offers the easiest and most efficient and safe production process to the assemblers.

Applications:
· All construction equipment machines
· Large injection moulding machines
· Agriculture and forestry machines
· Container handling machines
· High pressure cleaners
· Paper machines

Parker Parkrimp medium pressure fittings - 46series are compatible with the following hoses:
· 441 and 441RH
· 461LT
· 462, 462CLF, 462TC and 462ST
· 463
· 492 and 492ST
· 692 and 692Twin

TECH SPECIFICATIONS

TECHNOLOGY	Fluid & Gas Handling
SPECIFICATIONS MET	BS 5200-A
CONNECTION 1 TYPE	Hose
APPLICATION	Hydraulics
PORT TYPE	DKR

COATING	Chromium 6 Free-plated
CONNECTION 1 SIZE	9.5 mm (Size)
BODY MATERIAL	Steel
FITTING LENGTH	43 mm (see drawing legend A)
CONNECTION 1 SIZE	3/8 inch
DIVISION	Polymer Hose Division Europe
MAXIMUM OPERATING PRESSURE	55.0 MPa
CONNECTION 2 SIZE	3/8'-19 inch Thread
CONNECTION 1 SIZE	-6
SHAPE	Straight
CONNECTION LENGTH	20 mm (see drawing legend B)
INDUSTRY	Off-road Machinery
CONNECTION 2 TYPE	60° Cone
CONNECTION 2 TYPE	Swivel
INDUSTRY	Transportation
INDUSTRY	Industrial Manufacturing Equipment
HEX SIZE	22 mm (see drawing legend W)
DIVISION	Polymer Hose Division Europe
CONNECTION 2 TYPE	BSP Parallel Pipe
CONNECTION 2 TYPE	Female
BRAND	Parker
MAXIMUM OPERATING PRESSURE	550 bar