

Datasheet

RS Pro Stainless Steel Countersunk Head Machine Screws, M6 x 10mm

RS Stock No: **914-1692**



Product Details

RS Pro machine screw measuring M6 x 10 mm, is made of type 304 S15 A2 grade 18//8 stainless steel. The countersunk head screw can be used at up to 800°C. The slotted drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- A2 grade 18/8 stainless steel (Type 304 S15) construction
- Can be used up to 800°C
- Suitable for use in most food, medical, chemical, construction and electronic applications

Specifications:

Drive Type	Slot
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	10 mm
Stainless Steel Type	304 (A2)
Thread Pitch	1
Thread Size (Metric)	M6
Head Diameter	10.87 to 11.3 mm
Head Height	3.3 mm
Slot Depth	1.2 to 1.6 mm
Slot Width	1.6 mm
Specification	DIN 963