

# Eaton 058873

Catalog Number: 058873

Eaton Moeller® series RMQ16 Emergency-Stop label, Yellow, black lettering, Round, 60 mm, de, en, fr, it, Front dimensions 25 x 25 mm



General specifications

Product Name	Catalog Number
Eaton Moeller® series RMQ16	058873
Accessory Emergency-Stop label	EAN
	4015080588733
Product Length/Depth	Product Height
60 mm	1 mm
Product Width	Product Weight
60 mm	0.006 kg
Certifications	
UL/CSA certification not required	

## Product specifications

### Product Category

Accessories

#### 10.10 Temperature rise

Not applicable.

#### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

##### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

##### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

##### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Please enquire

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

## Resources

### Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-00004331.pdf](#)

[DA-DC-00004330.pdf](#)

### Drawings

[eaton-operating-emergency-rmq16-accessory-3d-drawing-002.eps](#)

[eaton-general-certificate-rmq16-standards.eps](#)

[eaton-operating-button-symbol-008.eps](#)

### Installation instructions

[IL04716016Z](#)

### mCAD model

[DA-CD-schild\\_r](#)

[DA-CS-schild\\_r](#)

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Connection to SmartWire-DT

No

#### Ambient operating temperature - max

60 °C

#### Ambient operating temperature - min

-25 °C

#### Equipment heat dissipation, current-dependent P<sub>vid</sub>

0 W

#### Heat dissipation capacity P<sub>diss</sub>

0 W

#### Heat dissipation per pole, current-dependent P<sub>vid</sub>

0 W

#### Outside diameter

60 mm

#### Rated operational current for specified heat dissipation (I<sub>n</sub>)

0 A

#### Static heat dissipation, non-current-dependent P<sub>vs</sub>

0 W

#### Size

25 × 25 mm

#### Color

Yellow

Shape

Round

Language

Several

Inscription

Other

Imprint ISO symbols

None



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



Eaton.com/socialmedia