

FEATURES

- Operating temperature range is between -25°C and 50°C
- Luminosity 4000lm
- Colour Temperature 6300K - daylight
- Fitting type is batten
- IK Rating – IK08
- Non-corrosive fitting (NCF)
- Made from high-quality Polycarbonate

LED Emergency Lighting Batten 40 W

RS Stock No.: 176-8554



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 4ft 40W LED Emergency Non-Corrosive Fitting comes with a high lumen output and are ideal for industrial and commercial applications such as warehouses, car parks, arenas and wet areas. With an ultra-durable Polycarbonate body and diffuser and aluminium tray they are extremely light and offer even light distribution. This light comes pre-fitted with stainless steel 304 anti-corrosion clips making them an ideal fitting for food preparation areas with an operating temperature range of -25 to +50°C.

General Specifications

Lamp Type	LED
Light Style	Downlight
Luminosity	4000lm
Lumen Efficiency	100lm/W
Colour Temperature	Daylight, 6300K
Maintained	Maintained
Beam Angle	120°
Material	Aluminium + Polycarbonate
Duration	3h
Applications	deal for commercial, industrial and retail applications and can be found in: Corridors, Workshops, Emergency exits, Carparks, Wet areas

Electrical Specifications

Wattage	40W
Voltage Rating	100V to 277V ac

Mechanical Specifications

Length	1.2 m
Width	94 mm
Fitting Type	Batten

Operation Environment Specifications

Environment Temperature	-25°C to 50°C
-------------------------	---------------

Protection Category

IP Rating	IP65
-----------	------

Approvals

Compliance/Certifications	RoHS, IK08
---------------------------	------------

