

Technical data


2304S

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	20 mm
D - External diameter	52 mm
B - Bearing/Inner ring width	21 mm
rs - Min fillet radius	1,1 mm
Radial clearance class	CN
Precision class	P0
Mass	0,207 kg

PRODUCT PERFORMANCE

C - Dynamic load	18500000 mN
C0 - Static load	4700000 mN
Cu - Fatigue limit load	210000 mN
e - Coefficient	0.5
Y0 - Static axial load coefficient	1.3
Y1 - Lower axial load coefficient	1.2
Y2 - Upper axial load coefficient	1.9
N lim - Oil lubrication limit speed	84000 °/s
N lim - Grease lubrication limit speed	66000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	26,5 mm
Da max - Max shoulder diameter OR	45,5 mm



2304S

Double-row self-aligning ball bearings

ABUTMENT	
ra max - Max shaft & housing fillet radius	1 mm