



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)








EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 <p>TE Part # 2-1719821-1 2POS,8MM HV,PLUG HSG,ASSY, CODB</p>	 <p>TE Part # 2297411-1 HV800 3POS PLUG CODE A 35SQ CABLE</p>	 <p>TE Part # 1-1991225-1 PROTECTIVE COVER. IPT 16-50mm sq. CABLE D</p>	 <p>TE Part # 1-1991225-2 PROTECTIVE COVER. IPT 16-50mm sq. CABLE D</p>
 <p>TE Part # 1991225-1 PROTECTIVE COVER. IPT 16-50mm</p>	 <p>TE Part # 2-1563316-1 3POS,8MM HV,PLUG HSG,ASSY, CODB</p>	 <p>TE Part # 1670820-1 SINGLE WIRE SEAL,PLUG TERM</p>	

Customers Also Bought

 <p>TE Part #4-2176614-7 EP 10W (SS) 82R 5% BULK BOX</p>	 <p>TE Part #1544603-1 1W 8MM NG1 SEALED CLIP ASSY BLACK</p>	 <p>TE Part #2324579-8 HOUSING, PLUG, 8P, DUAL ROW, EP2.5</p>	 <p>TE Part #172320-2 POSITIVE LOCK 250 (6.3 MM) HOUSING</p>
 <p>TE Part #4-2176331-3 CRGP 2512 33K 1%</p>	 <p>TE Part #170456-2 PL 250 AM REC 12-10 0.40 X 21 PRE- TPBR</p>	 <p>TE Part #172320-1 POSITIVE LOCK 250 (6.3 MM) HOUSING</p>	 <p>TE Part #1544227-1 CLIP 8 MM NG1-1 PO</p>
 <p>TE Part #1-2324579-2 HOUSING, PLUG, 12P,DUAL ROW, EP2.5</p>	 <p>TE Part #4-2176331-7 CRGP 2512 68K 1%</p>		

Documents



Product Drawings

SINGLE WIRE SEAL,8MM HV

German

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1719826-1\_A\_c-1719826-1-a.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1719826-1\_A\_c-1719826-1-a.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1719826-1\_A\_c-1719826-1-a.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

German