




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**  
Connector & Housing Type: **Tab Housing**  
Number of Positions: **2**  
Terminal Orientation: **Straight**  
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector & Housing Type	Tab Housing

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
------------------	------



Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	Nylon
Dimensions	
Product Length	28.5 mm[1.12 in]
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Industry Standards	
UL Flammability Rating	UL 94V-2
Packaging Features	
Packaging Quantity	500

Product Compliance

For compliance documentation, visit the product page on TE.com>











EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 <p>TE Part # 2348943-1 FF 187&amp;250 TAB HSG 9P NYLON NAT</p>	 <p>TE Part # 927357-1 FF 110 2P HOUSING PA66 NATURAL</p>	 <p>TE Part # 170349-1 FF 250 TAB 22-20AWG BR WITHOUT LATCH</p>	 <p>TE Part # 170340-3 FF 250 TAB 20-14AWG PTBR WITHOUT LATCH</p>
 <p>TE Part # 174198-1 FASTON .250 SERIES (6.3 MM) HOUSING</p>	 <p>TE Part # 170341-1 FF 250 TAB 14-12AWG BR WITHOUT LATCH</p>	 <p>TE Part # 170341-3 FF 250 TAB 14-12AWG PTBR WITHOUT LATCH</p>	 <p>TE Part # 170340-1 FF 250 TAB 20-14AWG BR WITHOUT LATCH</p>
 <p>TE Part # 927357-2 FF 110 2P HOUSING PA66 BLACK</p>	 <p>TE Part # 170349-2 FF 250 TAB 22-20AWG TPBR WITHOUT LATCH</p>		

Also in the Series | FASTIN-FASTON 250

 <p>Crimp Terminal Housings(195)</p>	 <p>Insertion &amp; Extraction Tools(2)</p>	 <p>Quick Disconnects(216)</p>
---	---	---

Customers Also Bought



TE Part #NB11652001  
ATUM-6/2-0-STK



TE Part #2160753002  
55A0111-24-5




TE Part #3870123006  
44A1111-18-9-9



TE Part #150545-2  
110 MINI FASTON,REC.,24-20 AWG, TPBR



TE Part #280919-4  
FF 187 REC 0.5-1.5MM2 TPPB



TE Part #CAT-55A-TC-H24  
General Purpose Hookup Wire: Tin Coated Copper Wire, 24 AWG



TE Part #CX7205-000  
RHW-48/12-1200/ADH-0



TE Part #735159  
250 PIDG FF

Documents

Product Drawings

FASTON .250 SERIES (6.3 MM) HOUSING

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_174197-1\_O.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_174197-1\_O.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_174197-1\_O.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English