

Eaton 188287

Catalog Number: 188287

Eaton Moeller® series MSC-DM DOL starter, 380 V 400 V 415 V: 3 kW, Ir= 6.3 - 10 A, 230 V 50 Hz, 240 V 60 Hz, Alternating voltage



General specifications

Product Name	Catalog Number
Eaton Moeller® series MSC-DM DOL starter	188287
	EAN
	4015081861729
Product Length/Depth	Product Height
76 mm	170 mm
Product Width	Product Weight
45 mm	0.58 kg

Certifications

CSA Class No.: 3211-04
CSA-C22.2 No. 14-10
IEC/EN 60947-4-1
UL60947-4-1A
VDE 0660
UL
CSA File No.: 012528
UL Category Control No.: NKJH
CSA
UL File No.: E123500
CE

Features & Functions

Fitted with:

Short-circuit release

Functions

Temperature compensated overload protection

General

Class

CLASS 10 A

Connection

Screw terminals

Connection to SmartWire-DT

No

Coordination type

1

Degree of protection

IP20

NEMA Other

Model

IEC/UL starter

Mounting method

DIN rail

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

1

Overload release current setting - min

6.3 A

Overload release current setting - max

10 A

Overvoltage category

III

Pollution degree

3

Rated impulse withstand voltage (Uimp)

6000 V AC

Suitable for

Also motors with efficiency class IE3

Type

Starter with Bi-Metal release

Voltage type

AC

Climatic environmental conditions

Altitude

Max. 2000 m

Ambient operating temperature - min

-25 °C

Ambient operating temperature - max

55 °C

Electrical rating

Rated operational current (I_e)

6.6 A

Rated operational current (I_e) at AC-3, 380 V, 400 V, 415 V

7 A

Rated operational power at AC-3, 220/230 V, 50 Hz

1.5 kW

Rated operational power at AC-3, 380/400 V, 50 Hz

3 kW

Rated operational voltage

230 - 415 V AC

Switching capacity (auxiliary contacts, general use)

1 A, 250 V DC, (UL/CSA)

15 A, 600 V AC, (UL/CSA)

Switching capacity (auxiliary contacts, pilot duty)

A600, AC operated (UL/CSA)

P300, DC operated (UL/CSA)

Short-circuit rating

Rated conditional short-circuit current (I_q), type 2, 380 V, 400 V, 415 V

0 A

Short-circuit release (I_{rm}) - max

155 A

Magnet system

Power consumption, sealing, 50 Hz

1.4 W, Dual-frequency coil in a cold state and 1.0 x U_s, at 50 Hz

Rated control supply voltage (U_s) at AC, 50 Hz - min

230 V

Rated control supply voltage (U_s) at AC, 50 Hz - max

230 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at DC - min

0 V

Rated control supply voltage (U_s) at DC - max

0 V

Design verification

Resources

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

Brochures

[eaton-motor-starters-system-xstart-brochure-br03407001en-en-us.pdf](#)

[eaton-msfs-motor-starter-feeder-system-brochure-br034005en-en-us.pdf](#)

Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Product Range Catalog Switching and protecting motors

Declarations of conformity

[DA-DC-00004246.pdf](#)

[DA-DC-00004937.pdf](#)

Drawings

[eaton-manual-motor-starters-msc-d-dol-starter-dimensions-002.eps](#)

[eaton-general-ie-ready-dilm-contactor-standards.eps](#)

[eaton-manual-motor-starters-msc-d-dol-starter-3d-drawing-002.eps](#)

[eaton-manual-motor-starters-mounting-msc-d-dol-starter-3d-drawing.eps](#)

eCAD model

[ETN.188287.edz](#)

Installation instructions

[IL034030ZU](#)

Installation videos

[WIN-WIN with push-in technology](#)

mCAD model

[DA-CS-msc_dm](#)

[DA-CD-msc_dm](#)

Sales notes

[eaton-link-module-for-motor-starters-pkz-flyer-fl034003en-en-us.pdf](#)

Wiring diagrams

[eaton-manual-motor-starters-device-msc-d-dol-starter-wiring-diagram.eps](#)

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)