

Features

- Bushing with Threaded Blind Hole and base plate: INOX AISI 304 stainless steel (corrosion-resistant, durable).
- Natural Rubber (NR), black color.
- 55 Shore A ± 5 (medium hardness for effective vibration damping).
- Damp vibrations, shocks, and noise from moving bodies or unbalanced vibrating masses.
- Prevents malfunctioning and extends machine lifespan.
- Reduces health risks caused by vibration exposure.
- Minimizes noise pollution.
- Ideal for equipment and machinery where vibration isolation is critical.
- Common in industrial, mechanical, and automation systems.

RS PRO RS PRO Rubber Buffer Bushing with Threaded Blind Hole and Base Plate in INOX AISI 304 Stainless Steel, Vibration-Damper Body in Natural Rubber NR, Black Colour, Hardness 55 Shore A ± 5



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Rubber Buffers Bushing with Threaded Blind Hole and Base Plate – INOX AISI 304 Stainless Steel

The RS PRO range of rubber buffers is designed to absorb vibrations, shocks, and noise in machinery and equipment. These buffers feature a natural rubber (NR) body with a hardness of 55 Shore A ± 5 , combined with INOX AISI 304 stainless steel bushing with threaded blind hole and base plate for excellent corrosion resistance and durability.

What are they used for?

- To isolate vibrations and reduce noise generated by moving parts or unbalanced rotating masses.*
- To protect machinery and surrounding structures from damage caused by shocks and vibrations.*
- To extend equipment lifespan and improve operational stability.*

Applications

Ideal for:

- Industrial machinery*
- Compressors, pumps, and generators*
- HVAC systems*
- Automation and assembly lines*

What are they used with?

Commonly paired with:

- Motors and engines to reduce vibration transmission.*
- Machine frames and bases for stability*
- Sensitive equipment to prevent operational disturbances.*

General Specifications

Material – Metal Parts	INOX AISI 304 Stainless Steel
Material – Buffer Body	Natural Rubber (NR), black color
Hardness	55 Shore A ± 5
Mounting Type	Bushing with Threaded Blind Hole
Corrosion Resistance	Yes (due to AISI 304 stainless steel)
Noise Reduction	Yes
Shock Absorption	Yes
Applications	Industrial machinery, compressors, pumps, HVAC systems

Similar Products

Stock No.	Diameter (mm)	Length (mm)	Thread Size	Hardness
0713764	20	17	M5	55
0713765	20	17	M6	55
0713766	25	17	M6	55
0713767	25	20	M6	55
0713768	32	22	M8	55
0713769	32	26	M8	55
0713770	38	32	M8	55
0713771	38	35	M8	55
0713772	38	35	M10	55
0713773	38	32	M10	55
0713774	43	50	M10	55
0713775	50	20	M10	55
0713776	50	43	M10	55
0713777	60	40	M10	55



