

## Product information

# 74 07 250

## High Leverage Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900

- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



⚡ 1000 V 



### General

|                 |                                     |
|-----------------|-------------------------------------|
| Article No.     | 74 07 250                           |
| EAN             | 4003773018421                       |
| Pliers          | chrome-plated                       |
| Head            | chrome-plated                       |
| Handles         | with dipped insulation, VDE-tested  |
| Weight          | 510 g                               |
| Dimensions      | 250 x 75 x 36 mm                    |
| Standard        | DIN ISO 5749 DIN EN 60900 IEC 60900 |
| REACH compliant | no                                  |
| RohS compliant  | no                                  |

### Technical details

|                                                |          |
|------------------------------------------------|----------|
| Cutting capacities medium hard wire (diameter) | Ø 4.6 mm |
| Cutting capacities hard wire (diameter)        | Ø 3.5 mm |
| Cutting capacities piano wire (diameter)       | Ø 3.0 mm |
| VDE tested                                     | yes      |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040302   |
| ETIM 5.0       | EC000165   |
| ETIM 6.0       | EC000165   |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1    | 27112114   |

technical change and errors excepted