



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Mount Orientation: **Inclined**

Connector System: **Wire-to-Device**

Number of Positions: **2**

Number of Rows: **1**

Centerline (Pitch): **5.46 mm [.214 in]**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector System	Wire-to-Device
Sealable	No
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Inclined
Number of Positions	2
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Mating Pin Diameter	1.5 mm[.059 in]
Contact Current Rating (Max)	7 A

Housing Features

Centerline (Pitch)	5.46 mm[.214 in]
--------------------	------------------



Usage Conditions

Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	450
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

E1 DIRECT DIESEL INJ CONN

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1337213-3\_C.2d\_dxf.zip

1337213-3

Inclined, Wire-to-Device, 2 Position, 5.46 mm [.214 in] Centerline, Power & Signal, Natural, Box



English

Customer View Model

[ENG\\_CVM\\_CVM\\_1337213-3\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1337213-3\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Product Datasheet](#)

English