

P82F 3/2 Soft Start/Dump Valve Excelon® Plus Modular System

- Port size: 1/4" ... 3/8" (ISO G/PTF)
- Excelon® Plus design allows in-line installation or modular installation with other Excelon® Plus products
- High forward flow capacity

- > Fast Exhausting
- Variable Snap Adjustment



Technical features

Medium:

Compressed air only

Maximum supply pressure:
10 bar (145 psi)

Minimum operating pressure:
3 bar (43 psi)

Port size:
G1/4, G3/8,
1/4 PTF, 3/8 PTF

Flow:

21 dm³/s at port size 1/4" Full flow P1 to P2 at 6,3 bar (91 psi) inlet, with 0,5 bar (7 psi) pressure drop P2 to P3 at 18 dm³/s

Ambient/Media temperature:

-20 ... +65°C (-4 ... +149°F) Air supply must be dry enough to avoid ice formation at temperatures below +2°C (+35°F).

Materials:

Body: Aluminium End Caps: Aluminum Body covers: ABS Elastomers: NBR Valve: Brass

Technical data P82F

Symbol	Port Size	Function	Voltage	Exhaust Port	Weight (kg)	Model
10 2 12 12 W T T T T T T T T T	G1/4	3/2 Soft Start	24 V d.c.	PTF 1/4	0,45	P82F-2GT-PFN
1 3	G3/8	3/2 Soft Start	24 V d.c.	PTF 1/4	0,45	P82F-3GT-PFN


Electrical details for solenoid operators

Voltage tolerance:	-10%/+15%
Rating:	100% continuous duty
Inlet orifice:	0,8mm
Electrical connection:	15mm DIN EN 175301-803 (DIN 43 50) Table C
Manual override:	Shrouded push button, spring return
Protection class:	IP65
Materials:	PP5 (body), NBR (seals)






Option selector




Flow characteristics

Port 1 to 2 Port size: 1/4"









Accessories





	Description	Cable length (m)	Model
		0,6	NC-DINCA-123MS-A
	PUR-Cable; M12/valve	1	NC-DINCA-123MS-1
typ	type C DIN connector	2	NC-DINCA-123MS-2
		5	NC-DINCA-123MS-5

Plug with with moulded cable and indicator



Voltage	Cable length (m)	Model
12 - 24 V a.c. / d.c	1	V10014-D01
12 - 24 V a.c. / d.c	3	V10014-D03
110 V a.c. / d.c.	1	V10015-D01
110 V a.c. / d.c.	3	V10015-D03
220 V a.c. / d.c	1	V10016-D01
220 V a.c. / d.c	3	V10016-D03

Plug with moulded cable

Description	Cable length (m)	Model
3 pin plug with moulded cable	1	V10013-D01
3 pin plug with moulded cable	3	V10013-D03

Light Emitting Seals ,15mm form C



Description	Model
Light Emitting Seals Circuit A (12 - 24 V d.c.)	V10037-E13
Light Emitting Seals Circuit B (110 - 120 V a.c.)	V10037-E18
Light Emitting Seals Circuit B (220 - 240 V a.c.)	V10037-F19

Plug with cable gland and indicator



Description	Model
Plug with cable gland and indicator 12-24 V a.c. / d.c., c/w LED / VDR	V10012-D13
Plug with cable gland and indicator 110 V a.c. / d.c., c/w LED / VDR	V10012-D18
Plug with cable gland and indicator 220 V a.c. / d.c., c/w LED / VDR	V10012-D19

M12 Adaptor Top - MSUP Valve Plug Form C 8MM




7000-42831-0000000

M12 Adaptor Rear - MSUP Valve Plug Form C 8MM



7000-42811-0000000





V10027-D00



Accessories

















- *1) Flanged version. For other pressure ranges, please see data sheet 5.11.001
- $^{\star}2)$ For other pressure ranges, please see data sheet 5.11.385









Silencer





Voltage rating and spare coils


	Voltage	Power	Replacement
() (-3.0070436) () (-3.0070436) () () () () () () () () () ()	24 V d.c.	1,2 W	840650-50KIT
See Assessment of the second s	110 V a.c.	1,5 VA	840650-51KIT
CE CONTRACTOR OR TO THE PARTY OF THE PARTY O	220 V a.c.	1,5 VA	840650-52KIT



Dimensions


Dimensions in mm Projection/First angle







1/4" exhaust port (NPT or ISO G)














Accessories


Quikclamp® with wall bracket







Quikclamp®










Pressure sensing block





Full flow porting block








Porting block for 18D pressure switch


18D Pressure switch


Dimensions in mm Projection/First angle


















18D Porting block and 18D assembled

Pipe adaptor











Silencer




Α	В	С	D	$\Sigma =$	Model
R1/4	17	92	32	32	MB002B
1/4 NPT	17	92	32	32	MB002A





51D Pressure switch - digital











- 1 Switch OUT 1, green LED
- 2 Switch OUT 2, red LED
- 3 Dustproof protector
- 4 Connector M12 x 1
- 5 Inlet port
- 6 Alternative inlet port G1/8 plugged
- 7 Thread for mounting screw

Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under »Technical features/ data«.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult Norgren Ltd.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.