

**3NA3130** LV HRC FUSE LINK 500V S.1 100A

As of 2012-02-18

LV HRC FUSE LINK GL/GG WITH NON-INSULATED GRIP LUGS WITH FRONT INDICATOR SIZE 1, 100A, AC 500V/DC 440V





Similar to image

Technical data:		
Current / for AC / rated value	A	100
Operating class of the fuse link		gG
Size of the fallback-system / acc. to DIN EN 60269-1		NH1
Supply voltage		
<ul style="list-style-type: none"> <li>for AC / rated value</li> <li>for DC</li> </ul>	V	500
	V	440
Switching capacity current		
<ul style="list-style-type: none"> <li>in accordance with IEC 60947-2 / rated value</li> <li>with DC / in accordance with IEC 60947-2 / rated value</li> </ul>	kA	120
	kA	25
Design of an identification indicator		Front indicators
Ambient temperature		
<ul style="list-style-type: none"> <li>minimum</li> <li>maximum</li> </ul>	°C	-5
	°C	40

### Certificates/approvals:

General Product Approval		Declaration of Conformity		Test Certificates	Shipping Approval
<input checked="" type="checkbox"/> KEMA	ROSTEST	<input checked="" type="checkbox"/> VDE	Manufacturer	Manufacturer	<input checked="" type="checkbox"/> GL (Germanischer Lloyd)
<b>other</b>					
Manufacturer					

### Further information:



**last change:**

Aug 26, 2011