

OYA510-02-4-12-P-4-M



Type of light

infrared light



Safety light grids

OYA510-02-4-12-P-4-M

Electrical design	PNP	
Protection	IP 65; IP 67	
Electrical data		
Operating voltage	[V]	24 DC
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 10
Type of light		infrared light
Wave length	[nm]	950
Receiver		
Current consumption	[mA]	84
Transmitter		
Current consumption	[mA]	42
Outputs		
Electrical design		PNP
Number of OSSD outputs		2
Max. current load per OSSD output	[mA]	300; (24 V)
Short-circuit protection		yes
Detection zone		
Protected area height	[mm]	510
Number of beams		2
Protection area width (low light intensity)	[m]	0...4
Protection area width (high light intensity)	[m]	3...12
Response times		
Response time	[ms]	5.5
Operating conditions		
Applications	class C to EN 60654-1 weatherproof application	
Ambient temperature	[°C]	-30...55
Storage temperature	[°C]	-30...70
Max. relative air humidity	[%]	95; (non condensing)
Protection	IP 65; IP 67	
Tests / approvals		
EMC	IEC 61496-1	
Shock resistance	IEC 61496-1	
Vibration resistance	IEC 61496-1	
Safety classification		
ESPE type (IEC 61496-1)	4	
Complies with the requirements	ISO 13849-1: 2015 category 4, PL e	
	IEC 61508 SIL 3	
	IEC 62061 SIL 3	
Mission time TM	[h]	175200



Safety light grids

OYA510-02-4-12-P-4-M

PFH	[1/h]	9E-09
-----	-------	-------

Mechanical data

Weight	[g]	4720
Dimensions	[mm]	685 x 50 x 55
Materials		housing: aluminium; front pane: PC
Length L	[mm]	685

Displays / operating elements

Display	transmitter	1 x LED
	receiver	10 x LED

Accessories


Items supplied	mounting bracket: 4
	slot nuts: 4

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection - receiver

Connection



Connector: 1 x M12; Maximum cable length: 100 m; for wire cross-section 1 mm²




Safety light grids

OYA510-02-4-12-P-4-M

Electrical connection - transmitter

Connection



Connector: 1 x M12; coding: A

