



EMI & EMC Solutions > IEC Inlets > Power Entry Modules



Filter Type: **Power Entry Module**  
Input Voltage Selection: **Quad AC**  
Filter Switch Type: **No Switch**  
Filter Shield Type: **Filter Shield**  
Product Orientation: **Vertical**

Features

Product Type Features

|                         |                    |
|-------------------------|--------------------|
| Ground Choke Option     | No                 |
| Filter Type             | Power Entry Module |
| Filter Switch Type      | No Switch          |
| Output Termination Type | .110" FASTON       |
| Filtering Requirements  | Filtered           |
| Filter Connector Type   | IEC 320/C-14       |

Configuration Features

|              |        |
|--------------|--------|
| Fuse Options | Single |
|--------------|--------|

Electrical Characteristics

|                                      |                                    |
|--------------------------------------|------------------------------------|
| Input Voltage Selection              | Quad AC                            |
| Leakage Current (Max) (120VAC, 60Hz) | 2 $\mu$ A                          |
| Leakage Current (Max) (250VAC, 50Hz) | 5 $\mu$ A                          |
| Current Rating                       | 6 A                                |
| Operating Voltage                    | 100 VAC, 120 VAC, 230 VAC, 240 VAC |

Body Features

|                     |               |
|---------------------|---------------|
| Filter Shield Type  | Filter Shield |
| Product Orientation | Vertical      |

Mechanical Attachment

|                          |        |
|--------------------------|--------|
| Panel Mount Feature Type | Flange |
|--------------------------|--------|



Product Compliance


For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JUN 2020 (209)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                 |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Corcom L



Customers Also Bought



TE Part #ZPF000000000015789  
DTB 26 B 11-01 AN



TE Part #4-1609155-2  
PE0S0DMXE=C7106



TE Part #4-2176215-6  
CPF A 0402 82K 0.1% 25PPM 1K RL



TE Part #8-2176305-5  
RP 1E 0.1W 806R 0.1% 25PPM 5K RL



TE Part #1-5146893-2  
1FHR,84,50A/S,S,C,S08,09,10



TE Part #6609104-4  
PE0S0SS60=C1129



TE Part #2-1611004-4  
3100-20T18999CL=40A 2P 120V PR



TE Part #5415105-2  
JACK,R/A,75 OHM,BNC PCB



TE Part #5788794-2  
25 HTMSFL PLUG RA 318 (IN,BL)



TE Part #6-1546158-7  
6PCV-13-007=0.375 SERIES #6 TR

Documents

Product Drawings

6EHL4 J0=F7420

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_6609123-5\_L.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_6609123-5\_L.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_6609123-5\_L.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1654001\_CORCOM\_PRODUCT\_GUIDE\_L\_SERIES

English

Corcom Combined Selector Charts

English