



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (.2% in 4674568) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #4-794619-2
12P MICRO MNL ASSY,R/A,HDR LF



TE Part #827001-2
4P MNL STIFTSOCKEL




TE Part #826936-2
2P AMPMODU II STIFT LEI




TE Part #350827-4
06P UMNL HDR ASSY PC 94VO LF




TE Part #2-1445099-3
MICRO MNL HDR ASSY S/ROW LF



TE Part #154717-E
SMCB 12 F AB VV 7-03 CL * H007 137 E002



TE Part #354063-E
SMCB 20 F AB VV 7-03 CL * H007 137 E002



TE Part #154720-E
SMCB 68 F AB VV 7-03 CL * H007 137 E002



TE Part #826469-3
2X3P MOD II SHROUDED HEADER, ST



TE Part #3-794626-8
08P MICRO MNL ASSY,R/A,SMT,LF

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1106416-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1106416-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1106416-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English