

Specifications



Eaton 107413

Eaton Moeller® series M22 Bulkhead interface, RJ45 socket, 8/8, cat. 5e, Bezel: titanium

General specifications

PRODUCT NAME	Eaton Moeller® series M22 Accessory Bulkhead interface
CATALOG NUMBER	107413
MODEL CODE	M22-RJ45-SA
EAN	4015081071517
PRODUCT LENGTH/DEPTH	30 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.014 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	UL 508 CSA Std. C22.2 No. 142 IEC 6113-2 UL report applies to both US and Canada Certified by UL for use in Canada IEC/EN 6113-2 UL File No.: E330994 UL CSA Class No.: none CSA-C22.2 No. 142 UL Category Control No.: DUXR, DUXR7 CE
CATALOG NOTES	RJ45 socket, 8/8, cat. 5e
GLOBAL CATALOG	107413



Powering Business Worldwide

Product specifications

ACCESSORY/SPARE PART TYPE	Accessory
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND	Meets the product

Resources

	Flip catalog - Product Range Catalog - Command and indication
	eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf
CATALOGS	eaton-rmq-titan-brochure-br047004en-en-us.pdf
DRAWINGS	eaton-operating-m22-bulkhead-interface-dimensions-002.eps eaton-operating-m22-bulkhead-interface-3d-drawing.eps
ECAD MODEL	DA-CE-ETN.M22-RJ45-SA
FLYERS	eaton-rmq-titan-selection-aid-brochure-fl047002-en-us.pdf
INSTALLATION INSTRUCTIONS	IL04716002Z
INSTALLATION VIDEOS	RMQ Flat Design
MCAD MODEL	DA-CS-rj45 DA-CD-rj45
MULTIMEDIA	MCI Multicolor Light Indicator M22 with SmartWire-DT easyE4 SmartWire-DT module with Remote Touch Display and RMQ multi color indicator MCI MultiColor Light Indicator RMQ compact solution RMQ small E-Stop emergency-stop button
	eaton-control-circuit-devices-rmq-titan-fl144090en-en-us.pdf
	eaton-rmq-small-e-stop-flyer-fl047006en-en-us.pdf
SALES NOTES	eaton-rmq-flat-enclosure-flyer-fl047003en-en-us.pdf eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf

CREEPAGE DISTANCES	standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
CONTACT MATERIAL	CuSn, gold-plated
CONNECTION TO SMARTWIRE-DT	No
BEZEL COLOR	Titanium
CONTACT TYPE	1:1
MATERIAL	Titanium front ring
DESIGN	RJ45
DEGREE OF PROTECTION	IP65 (with closed cover) IP20 (with plug connected) NEMA 12 (with closed cover)
ELECTRICAL ACCESSORY TYPE	Other
RATED OPERATIONAL VOLTAGE	24 V AC
RESISTANCE	< 30 mΩ (volume resistance)
MECHANICAL ACCESSORY TYPE	Other
INSULATION RESISTANCE	≥ 100 MΩ
LIFESPAN, MECHANICAL	750 insertion cycles
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-25 °C

WIRING DIAGRAMS

[eaton-operating-connection-m22-bulkhead-interface-wiring-diagram.eps](#)

FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
MOUNTING DEPTH	70 mm
NOMINAL CURRENT	1500 A
LIMIT VALUE CLASS	5
NOMINAL VOLTAGE - MAX	50 V
OPENING DIAMETER	22.5 mm
NUMBER OF POLES	Eight-pole

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

