



22MM PLASTIC ROUND COMPLETE UNIT
 COMBINATION: ILLUMINATED PUSHBUTTON WITH FLAT
 BUTTON NON-ILLUMINATED WITH LAMP HOLDER BA 9S
 WITHOUT LAMP SPRING-LOADED TERMINAL,
 1NO WITH HOLDER BLUE

Front ring:

| | | |
|--------------------------------|--|---------|
| Product component / front ring | | Yes |
| Material / of the front ring | | plastic |
| Color / of the front ring | | black |

Enclosure:

| | | |
|------------------------------|--|---------|
| Shape / of the housing front | | round |
| material / of the housing | | plastic |

General technical details:

| | | |
|--|---|-------------------------|
| Number of control points | | 1 |
| Type of voltage | | AC/DC |
| • of the operating voltage | | |
| Operating voltage / rated value | | |
| • minimum | V | 5 |
| • maximum | V | 400 |
| Design of the electrical connection | | spring-loaded terminals |
| Number of switching positions | | 2 |
| Product component / fluorescent materials | | No |
| Product extension / optional / fluorescent materials | | Yes |

| | | |
|--|-----|-------------------|
| Resistance against shock | | |
| <ul style="list-style-type: none"> • for devices with incandescent lamp / according to IEC 60068-2-27 | | <= 30g |
| <ul style="list-style-type: none"> • for devices without incandescent lamp / according to IEC 60068-2-27 | | <= 50g |
| Resistance against vibration / according to IEC 60068-2-6 | | 20 ... 200 Hz: 5g |
| Operating cycles / maximum | 1/h | 1,000 |
| Mechanical operating cycles as operating time / typical | | 3,000,000 |
| Item designation | | |
| <ul style="list-style-type: none"> • according to DIN EN 61346-2 | | S |
| <ul style="list-style-type: none"> • according to DIN 40719 extendable after IEC 204-2 / according to IEC 750 | | S |

Auxiliary circuit:

| | | |
|--|--|---|
| Number of NC contacts / for auxiliary contacts | | 0 |
| Number of NO contacts / for auxiliary contacts | | 1 |
| Number of change-over switches / for auxiliary contacts | | 0 |

Installation/mounting/dimensions:

| | | |
|---|-----|---------------------|
| Execution of the mounting | | BA 9s, without lamp |
| Type of mounting | | front mounting |
| Shape / of the installation hole | | round |
| Installation width | mm | 28.5 |
| Mounting diameter | mm | 22 |
| Mounting height | mm | 8 |
| Tightening torque / of the screws in the bracket / maximum | N·m | 1 |

Ambient conditions:

| | | |
|--|----|------------|
| Ambient temperature | | |
| <ul style="list-style-type: none"> • during operating | °C | -25 ... 60 |
| <ul style="list-style-type: none"> • during storage | °C | -40 ... 80 |
| Protection class IP | | IP66 |

Certificates/approvals:

General Product Approval



CQC



CSA

[ROSTEST](#)



UL

Test Certificates

[Manufacturer](#)

Shipping Approval



ABS



BUREAU
VERITAS



DNV



LRS



PRS



RINA

other

[Manufacturer](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAX-Online-Generator

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3206-0AA51-0CC0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3206-0AA51-0CC0

last change:

Oct 31, 2011