

Endress+Hauser Display RIA15-8AC3

Field or panel indicator for 4 to 20 mA or HART® process values.



Picture for reference only. Product appearance may vary based on configuration

The loop-powered process indicator RIA15 displays 4 to 20 mA measured values or optionally up to four of a sensor's HART® process variables in all industries. The RIA15 has 5-digit measured value display with 17 mm (0.67 in) digit height with dimension, bar graph and activatable backlighting and can be use for panel-mount housing or field housing as local display.

- Easy configuration and on-site parameter setup with 3 front-mounted key push buttons.
- No external power supply is necessary, the device is powered directly from current loop.
- Perfect solution if measuring points are difficult to access, especially if long wiring distances are required / Voltage drop < 1V
- Interrogates up to 4 different measurement values in a running process and displays them (via HART protocol).
- Low installation depth

Configuration of RIA15-8AC3:

Approval:	8A	ATEX IECEx II2(1)G Ex ib [ia Ga] IIC T6
Housing:	C	Field housing plastic 131x81.5x55.5mm
Input:	3	4-20mA current signal + HART + level, option for FMR20 + FMR20B + FMR30B + FMX21 + FMG50

Alternative part number: RIA15-24V1/0