

# TMG -5, TJG-5 SERIES


5x5 SMT & J SMT  
(H: 0.8 & 1.5mm)



TACT SWITCH



## HOW TO ORDER



## SPECIFICATION

### MECHANICAL

Operation Force: 260±50gf  
160±50gf  
100±50gf  
70±30gf

Stroke: 0.25±0.1 mm/- 0.2 mm

### ENVIRONMENTAL

Operation Temperature Range : -25°C to +70°C

Storage Temperature Range : -30°C to +80°C

### ELECTRICAL

Electrical Life:

1,000,000 cycles min. for 70gf, 100gf, 160gf

200,000 cycles min. for 260gf


Rating : 50mA, 12VDC

### PACKAGE

Tape and Reel: 4000 pcs/reel




## CIRCUIT

WITHOUT GROUND  
CIRCUIT DIAGRAM






WITH GROUND  
CIRCUIT DIAGRAM

## TMG-53



## TMG-52



General Tolerance: ±0.2mm( ±0.008")