Technical sheet

BTC60TR


Modular barrier Ø 60mm – 3-sided post

Modular warehouse barrier designed to ensure safety in industrial areas. It helps to organise vehicle traffic and demarcate high-risk zones, whilst ensuring the protection of people. Made from galvanised steel and coated with yellow epoxy paint. These various components allow for the creation of 'customized' paths:

- Available in 40 mm or 60 mm diameter tubing,
- Various post types: straight, corner, 2-sided or 3-sided,
- Various gate types: wicket gate or swing gate

Fixings available as options.





Customs code	7326909890
EAN	3321360116451

Color : Yellow

Material : Galvanized steel

Specifications :

- Triple post (on 3 sides of the post) for modular barrier.
- Tube diameter 60 mm.
- Fixing plate 150 x 150 mm.
- 4 fixing holes Ø 14 mm.
- Fixings optional.
- Do not install in saline or hydrocarbon environments.

Length (mm)	Width (mm)	Height (mm)	Dimensions plate (mm)	Net weight (kg)
380	200	1000	150 x 150	5,40

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com