





JAS, Speed Controller with One-touch Fitting, Compact, Push-lock Type

JAS-LEA04-M3

Datasheet

- Elbow type.
- Oval release.
- Applicable tubing O.D.: Ø 3.2 to Ø 6.
- Operating pressure range: 0.05 to 0.7 MPa.
- Ambient and fluid temperatures: -5 to 60 °C.




Flow control valve, adjustable, with reverse free flow



Standard specifications

Control Method	E (Meter-out, Gray)
Stud Position	A (Right Side)
Applicable tubing O.D.	04 (ø4)
Port Size	M3 (M3 x 0.5)
Seal method	w/o Sealant
Pressure medium	Air
Maximum operating pressure	0.7 MPa
Minimum operating pressure	0.05 MPa
Proof pressure	1.05 MPa
Maximum ambient temperature	60 °C
Minimum ambient temperature	- 5 °C
Usable tubing material	Nylon, Soft Nylon, Polyurethane, FEP, PFA
Weight	0.005 Kg

Dimensions



Constructions



Component Parts

No.	Description	Material	Note
1	Body A	PBT	
2	Body B	PBT	
3	Needle	PBT	
4	Knob	POM	
5	Stopper	Stainless steel	
6	Needle guide	Brass	Electroless nickel plating
7	Disk seal	HNBR	
8	Stud	Brass	Electroless nickel plating
9	O-ring	NBR	
10	O-ring	NBR	
11	O-ring	NBR	
12	Cassette	—	
13	Seal	NBR	
14	O-ring	NBR	Meter-in only
15	Gasket	NBR/Stainless steel	
16	Seal	NBR	

Additional information

Catalogue	JAS-B_EU.pdf
Operation manuals	OM_ASx_OMX0006EN.pdf