



Image may differ from product. See technical specification for details.

NA 2203.2RS

Support roller (yoke-type track roller), without flange rings, with integral sealing

Support rollers (yoke-type track rollers) are designed to run on all types of tracks and to be used in cam drives, conveyor systems, etc. They are based on a single row needle roller bearing with an inner ring and have a thick-walled outer ring with a crowned running surface. They are supplied sealed and are ready-to-mount. The inner ring contains a

lubrication hole to facilitate relubrication. The inner ring can be mounted separately from the outer ring and roller and cage assembly.

- High radial load carrying capacity
- Able to withstand shock loads
- Ready to mount
- Separable design
- Integral sealing prolongs bearing service life

Overview

Dimensions

Functional outside diameter	40 mm
Bore diameter	17 mm
Width, total	16 mm
Width, outer ring	15.8 mm

Performance

Basic dynamic load rating	9.52 kN
Basic static load rating	13.2 kN
Limiting speed	4 500 r/min


Properties

Bearing part	Complete track roller
Rolling elements	Needle rollers
Number of rows	1
Outer ring profile	Crowned
Axial guidance of outer ring	Yes
Number of flanges, outer ring	2
Cage	With
Radial internal clearance	CN
Tolerance class	Other
Material, bearing	Bearing steel
Coating	Without
Sealing	Seal on both sides
Sealing type	Contact
Lubricant	Grease
Relubrication feature	With

Logistics

Product net weight	0.112 kg
eClass code	23-05-09-03
UNSPSC code	31171512

Technical specification



Dimensions

D	40 mm	Outside diameter
d	17 mm	Bore diameter
C	15.8 mm	Width outer ring
B	16 mm	Width inner ring
D ₁	28 mm	Recess diameter outer ring shoulder
F	22 mm	Raceway diameter inner ring
r _{1,2}	min. 1 mm	Chamfer dimension outer ring
r _{3,4}	min. 0.3 mm	Chamfer dimension inner ring

Calculation data

Basic dynamic load rating	C	9.52 kN
Basic static load rating	C ₀	13.2 kN
Fatigue load limit	P _u	1.6 kN
Maximum dynamic radial load	F _r	max. 15.3 kN
Maximum static radial load	F _{0r}	max. 22 kN
Limiting speed		4 500 r/min

Tolerances and clearances

GENERAL SUPPORT ROLLER SPECIFICATIONS

- [Tolerances: Normal, Other](#)
- [Radial internal clearance: table](#)

BEARING INTERFACES

- [Seat tolerances for standard conditions](#)
- [Tolerances and resultant fit](#)

More Information

 Product details Designs and variants Lubrication General support roller specifications Loads Temperature limits Speed limits Design considerations Mounting Designation system	 Engineering information Principles of rolling bearing selection General bearing knowledge Bearing selection process Bearing interfaces Lubrication External sealing, mounting and dismounting Bearing failure and how to prevent it	 Tools SKF Product select Bearing Frequency Calculator SimPro Quick LubeSelect for SKF greases Heater selection tool
--	---	---



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.