

24V LDO

Product Brief

TLT807B0EPV

OPTIREG[™] Linear voltage regulator for 24 V applications Low dropout adjustable stand-by linear voltage regulator with overvoltage protection

The TLT807B0EPV is a 70 mA low dropout linear voltage regulator with enable feature. The 70 mA regulator has an adjustable output voltage and is available in a TSDSO-14 package.

The wide input voltage range and the low quiescent current make it perfectly suitable for supply systems connected permanently to the battery. The overvoltage protection feature allows for the device to be used in 24 V automotive applications (e.g. trucks, commercial vehicles etc.). With a 58 V load dump capability the device is perfectly suited to supply loads in stand-by mode in 24 V applications.

The TLT807B0EPV has an integrated enable function and can be switched on and off via the enable pin. The current consumption in OFF mode is limited to 1.5 μ A. The device is stable with a small 1 μF output capacitor.

The device also includes internal protection features such as output current limitation and overtemperature shutdown. The main benefit of this product is that it has been qualified according to AEC-Q100 Grade 1 for extended mission profiles and has been qualified for automotive applications with extended lifetime requirements.

TLT807 5 V, up to 0.07 A Stand-by 5 V, up to 2.3 A **TLS208** Adjustable, up to 0.8 A ain supply POST **TLE6389 TLS205** Adjustable, up to 0.5 A

POST

TLS202

POST

Application diagram for TLT807B0EPV as a stand-by supply for 24 V ECUs



Key features

- > Enable
- > Adjustable output voltage

OPTIREG

Linear

- > Output voltage accuracy: 2 percent
- > Output current: 70 mA
- > Current consumption: 36 µA
- > Overvoltage protection up to 58 V
- > Available in TSDSO-14 package
- > Wide operating temperature range: $-40^{\circ}C \le T_i \le 150^{\circ}C$

Benefits

- > Load dump voltage up to 58 V → **Requirement for 24 V battery** powered applications
- > Robust TSDSO-14 package → Longer lifetime requirements for trucks, commercial and agricultural vehicles
- > Low dropout voltage and quiescent current \rightarrow Suitable as a stand-by supply
- > Extended qualification strategy for longer lifetime requirements

Applications


- > Stand-by linear voltage regulator for
 - xEV applications
 - 24 V applications
- Trucks, commercial vehicles, construction vehicles, agricultural vehicles



TLT807B0EPV

OPTIREG[™] Linear voltage regulator for 24 V applications

Low dropout adjustable stand-by linear voltage regulator with overvoltage protection



Product	OPN	Output current I _{out} [mA]	Quiescent current I _q [µA]	Enable	Overvoltage protection	Output voltage [V]	Package
TLT807B0EPV	TLT807B0EPVXUMA1	70	36	Yes	Yes	Adjustable	TSDSO-14

Evaluation board name	Evaluation board OPN	Description
TLT807B0EPV BOARD	TLT807B0EPVBOARDTOB01	Evaluation board for 70 mA stand-by linear voltage regulator for 24 V applications

Published by Infineon Technologies AG 81726 Munich, Germany

© 2019 Infineon Technologies AG. All Rights Reserved.

Please note!

THIS DOCUMENT IS FOR INFORMATION PURPOSES ONLY AND ANY INFORMATION GIVEN HEREIN SHALL IN NO EVENT BE REGARDED AS A WARRANTY, GUARANTEE OR DESCRIPTION OF ANY FUNCTIONALITY, CONDITIONS AND/OR QUALITY OF OUR PRODUCTS OR ANY SUITABILITY FOR A PARTICULAR PURPOSE. WITH REGARD TO THE TECHNICAL SPECIFICATIONS OF OUR PRODUCTS, WE KINDLY ASK YOU TO REFER TO THE RELEVANT PRODUCT DATA SHEETS PROVIDED BY US. OUR CUSTOMERS AND THEIR TECHNICAL DEPARTMENTS ARE REQUIRED TO EVALUATE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED APPLICATION.

WE RESERVE THE RIGHT TO CHANGE THIS DOCUMENT AND/OR THE INFORMATION GIVEN HEREIN AT ANY TIME.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

24V LDO

Ô Ô

OPTIREG

Linear

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any lifeendangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.