

Electrical specification:


Input: 207 - 253VAC, 50/60Hz
 Full load input current: 110mA
 Output: +/-15V @ 500mA max.

Output tolerance: +/- 0.6V (5mA - 500mA)
 Max. ripple / noise: 1mVrms
 Minimum load: 5mA
 Line / load regulation: ± 150mV

Isolation, primary to secondary: 3kVrms / 2s
 Primary protected by single shot 130°C thermal fuse.


All materials are UL94V-2 minimum
 Transformer insulation class B min.



Designed in accordance with:
 BS EN61558-2-6:2009
 Low Voltage Directive CE93/68/EEC
 Low Voltage Directive CE 73/23/EEC
 EMC Directive CE 89/336/EEC



Unit 5, Oxonian Park, Langford Locks,
 Kidlington, Oxfordshire. OX5 1FP
 Tel: (01865) 855085 Fax: (01865) 855075
 Website: www.oep.co.uk


DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
Specification for PS2127 Page 1 of 2	1	14/08/14	CS		PS2127
	2	23/01/15	CS		
Scale: nts					





Chassis mounting:


To chassis mount, remove 4 x M2.5 screws from base plate.
Maximum screw length: 8mm



Terminal specification:


Terminal: brass, 0.8t tin plated
Screw: steel, M4 Ni, plated
Wire range: 22-12 AWG
Max. torque 1.2Nm

All materials are UL94V-2 minimum
Transformer insulation class B min.



Approximate mass: 0.78kg

Tolerance on all dimensions: +/- 0.3mm unless stated otherwise



Unit 5, Oxonian Park, Langford Locks,
Kidlington, Oxfordshire. OX5 1FP
Tel: (01865) 855085 Fax: (01865) 855075
Website: www.oep.co.uk

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
Specification for PS2127 Page 2 of 2	1	14/08/14	CS		PS2127
	2	23/01/15	CS		
Scale: nts					