



Brand of NTN corporation

Technical data

UCFCE210

Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

KIT CONTENT

UC210G2, FCE210

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing height	25,5 mm
A1 - Housing foot height / flange height	13 mm
A2 - Total height from mounting surface	31,6 mm
A3 - Centering depth / chamfer dimension	3 mm
B - Width of Inner Ring	51,6 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

d - Shaft diameter	50 mm
e - Distance mounting surface to bearing center	-1 mm
G - Grease fitting	M8x1
H3 - Centering dia	110 mm
J - Mounting holes distance	135 mm
L - Housing width / diameter	165 mm
N - Mounting hole dimension	14 mm
S - Distance front side/bearing centre	19 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	35100000 mN
C0 - Static load rating	23200000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	2,2 kg
Recommended tightening torque for set screw	22 N-m

