

Product data sheet

Specifications



Repacked, miniature circuit breaker (MCB), Acti9 iC60L, 4P, 63A, C curve, 15kA (IEC/EN 60947-2)

A9F94463W



This repacked option saves 4.944 over the standard condition

Main

Range	Acti9
Product name	Acti9 iC60
Product or component type	Miniature circuit-breaker
Device short name	iC60L
Device application	Distribution
Poles description	4P
Number of protected poles	4
[In] rated current	63 A
Network type	AC DC
Trip unit technology	Thermal-magnetic
Curve code	C
Utilisation category	Category A conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Standards	EN/IEC 60947-2

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	12...133 V AC 50/60 Hz 220...240 V AC 50/60 Hz 380...415 V AC 50/60 Hz 440 V AC 50/60 Hz <= 250 V DC
Magnetic tripping limit	8 x In +/- 20 %
Breaking capacity	70 kA Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 20 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2
[Ics] rated service breaking capacity	35 kA 50 % x Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA 50 % x Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 7.5 kA 50 % x Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 5 kA 50 % x Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 20 kA 100 % x Icu at <= 250 V DC conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Clip-on Removable comb busbar installed
Mounting support	35 mm DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
Connection pitch	18 mm between phases
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	78.5 mm
Product weight	0.5 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Single terminal (top or bottom) , for 1 cable(s) , 1...35 mm², rigid, copper Single terminal (top or bottom) , for 3.0 cable(s) , 16 mm², rigid, copper, with accessory Single terminal (top or bottom) , for 1.0 cable(s) , 50 mm², rigid, aluminium, with accessory Single terminal (top or bottom) , for 1.0 cable(s) , 1...25 mm², flexible, copper Single terminal (top or bottom) , for 1.0 cable(s) , 1...25 mm², flexible with ferrule, copper Single terminal (top or bottom) , for 1.0 cable(s) , flexible, copper or aluminium, with ring terminal and accessory Single terminal (top or bottom) , for 3 cable(s) , 10 mm², flexible, copper, with accessory
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom
Earth-leakage protection	Separate block

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 in modular enclosure (Insulation class II) conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	0...2000 m
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	7.200 cm

Package 1 Length	9.500 cm
Package 1 Weight	528.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	8.000 cm
Package 2 Width	9.800 cm
Package 2 Length	22.500 cm
Package 2 Weight	1.645 kg
Unit Type of Package 3	S03
Number of Units in Package 3	33
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	18.574 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

26ff71d1-98cf-4280-8725-455b9a6b2fb9

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins