




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.65 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	.7 – 10.2 kgf

Dimensions

Product Length	22.3 mm[.88 in]
Compatible Insulation Diameter Range	2.3 – 3.3 mm[.09 – .13 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.51 – 1.65 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	5100
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 KIT TE Part # 7-2151182-7 OCEAN_2.0_SPARE_PART_KIT-090F130F	 TE Part # 654174-1 POS.LOCK HANDTOOL	 TE Part # 2151182-2 OCEAN_2.0_APPLICATOR-S-090F130F-RSA	 TE Part # 2836571-2 OCEAN_2.0_Applicator-S-090F130OV-RSA
 TE Part # 216331-2 .250 POS.LOCK L.I.F	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 5-2151182-2 OCEAN_2.0_APPLICATOR-S-090F130F-RSA	 TE Part # 626581-1 PL 250 REC 0.5-1.5 MM2 0.35X 26.54 BR
 KIT TE Part # 7-2836571-7 OCEAN_2.0_SPARE_PART_KIT-090F130OV			


Also in the Series | [Mark I](#)



Automotive Headers(5)



Automotive Terminals(1)



Crimp Terminal Housings(177)



Insertion & Extraction Tools(3)



PCB Headers & Receptacles(5)



Quick Disconnects(173)




Rectangular Power Connectors(2)




Wire-to-Board Headers & Receptacles (5)

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(177)



Insertion & Extraction Tools(3)




Insulation Boots & Sleeves(5)



Quick Disconnects(173)

Customers Also Bought





TE Part #3823823004
[44A0121-20-0/9](#)



TE Part #175196-3
[DYNAMIC D-3 REC CONT/L AU 0.76](#)



TE Part #3-1825137-6
[A105SYCB04](#)




TE Part #1718758-1
[MCON 1.2 LL TAB SWS SN](#)



TE Part #1-1924067-1
[2POS, MCON 1.2 CB REC 2p TL SEALED](#)



TE Part #1-1564559-1
[4POS, MCON 1.2 LL TAB SEALED COD A](#)



TE Part #3823313006
[44A0121-22-0/9](#)



TE Part #1587829-2
[OUTER FERRULE, SIZE B, HVA280-2PI](#)



TE Part #1587828-2
[INNER FERRULE, SIZE B, HVA280-2PI](#)



TE Part #1587827-3
[CABLE SEAL RETAINER, SIZE C, HVA280-2PI](#)

Documents

Product Drawings

[PL 250 TERMINAL REC 0.5-1.5 MM2 PHBZ](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_160759-2_AL.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160759-2_AL.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160759-2_AL.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

AMP positive lock MKI rec. terminal with latching device

Application Specification

EB**General Application Specification for Open Barrel Terminals

English

Application Specification

English

Agency Approvals

UL

English