

Description

A compact, economical, 6 figure, non-reset, electromechanical counter designed for general purpose industrial and commercial counting applications. It is designed for a variety of mounting methods as required by the application. Commonly used for coin-operating equipment, photocopiers and vending machines.

Features

- 6 figure
- Compact
- Non-reset
- Variety of mounting options

Options

- Voltages

Specifications

Figures: 6 figures, white on black, 0.17" [4.3mm] high
Reset: None
Speed: 1,000 counts/minute AC, (min. 30ms - on, 30ms - off)
 1,200 counts/minute DC, (min. 25ms - on, 25ms - off)
Power: AC: 24VAC ~ 4 watts
 115VAC ~ 3.5 watts
 230VAC ~ 5 watts
 DC: 12/24VDC ~ 2 watts

Mounting: Panel or base
Terminations: (2) #22 AWG 105°C wire leads, 12" [305mm] long
Operating Life: Beyond 10 million counts
Temp. Range: -15°F to +140°F [-26°C to +60°C]
Approvals: UL Recognized, CE Compliant, ROHS
Weight: 3.5 oz. [99g]

Models Description

P2-4816 115VAC, 6 figures, P panel mount
P8-4816 24VDC, 6 figures, P panel mount
V2-4816 115VAC, 6 figures, V base mount
V3-4816 24VAC, 6 figures, V base mount
V8-4816 24VDC, 6 figures, V base mount

Models Description

D2-4816 115VAC, 6 figures, D base mount

* Items in bold are normally in factory stock.

Applications

Control panels




Gaming machines



Vending machines



Coin-operated equipment




Photocopiers






Dimensions

D - Mount




Mounting holes: 0.15" [3.8] Dia.

P - Mount



Mounting holes: For #5 flat head screw
Panel cutout: 1.72" x 1.05" [43.7 x 26.7mm]

V - Mount



Mounting holes: 0.16" x 0.28" [4.1 x 7.1mm] slots