European Thermodynamics Limited



European Thermodynamics Limited

Intelligent Thermal Management

SEARCH

<u>Menu</u>

• Products

- Thermoelectric Modules
- Thermoelectric Cooler Modules
- Thermoelectric Generator Modules
- Energy Harvesting
- Energy Harvesting PCBs
- Thermoelectric Energy Harvesting Kit
- Energy Harvesting Solar Panel
- <u>Temperature Controllers</u>
- JUNIOR PID Thermal Controller
- CyCLO Servo PWM Thermal Controller
- PR-59 PID Thermal Controller
- Thermoelectric Assemblies
- Air to air thermoelectric assemblies
- Direct to air thermoelectric assemblies
- Thermal Interface Materials
- Gap Filler Pads / Sheets
- Graphite-based Interface Materials
- Phase Change Materials
- Thermal Grease / Putty
- Thermal Tape
- Heaters
- PTC heating elements
- Heating assemblies
- Convection heaters
- Heat Pipes
- Heat Pipes Grooved & Sintered
- Heat Pipes Grooved
- Heat Pipes Screen Mesh
- Heat Pipes Sintered
- Heat Sinks
- Ceramic Heat Sinks
- Plastic Heat Sinks
- Natural Convection Heat Sinks
- LED Heat Sinks
- DC to DC Heat Sinks
- Heat Sink Clips
- Forced Convection Heat Sinks
- Fans
- Axial fans
- Blowers
- Sensor & Instrumentation

Web user feedback

- Services
 - Design and development
 - Client Projects
- Resources
 - Articles
 - Technical Reference
 - o FAQ
- Markets
- Research ▼
 - Automotive
 - <u>Sensors</u>
 - Buildings
 - Manufacturing
 - Thermoelectric Materials
 - Industrial
 - Solar
 - Thermoelectic Cooling
 - Aerospace
 - Marine
- Stockists
- <u>Contact</u>
- About ▼
 - Careers
 - <u>People</u>
 - Group
- News

Products / Heaters / PTC heating elements / PTC heater 20W

PTC heater 20W

FG14756.1

Features

- Allows high power densities in a compact design
- HP elements may be installed through the use of clamps or bolts, held in place by the mounting notches on the wings of the aluminium extrusion itself
- A double sided pressure sensitive adhesive may also be used in applications with a surface temperature of up to 302 deg;F / 150 deg;C

Specifications

Power (W) 20

Temperature DegC 40

Voltage (V) 11232

Width mm 35 Height mm 40

Depth mm 8.3

Request information Data sheet

Buy online









Tweet



For further information, contact us

Contact

y in ∰ 8⁺

- Products
- <u>Services</u>
- Resources
- Markets
- Research
- Stockists
- About
- News
- Contact
- Terms
- <u>Disclaimer</u>
- Privacy Policy
- Conflict Minerals Policy
- Careers
- © 2020 European Thermodynamics Ltd.